



Philips
Electret Microphone

SBCME570



Studio quality

Liven up the occasion with an electret microphone for studio-quality recordings.

Bring the occasion to life

- Electret condenser ensures studio quality sound and clarity
- Minimized noise when switching between on and off
- Omni-directional design picks up sound from all directions
- Windshield improves sound quality by preventing noise

Always ready

- A 5m-long cable that's ideal for use with microphones
- Die-cast housing reduces resonance and extends product life
- Convenient box for microphone and cable storage
- Table stand allows hands-free use on a flat surface

PHILIPS

Specifications

Sound

- Frequency response: 50 - 18 000 Hz
- Impedance: 600
- Polar pattern: Omni directional
- Sensitivity microphone: -45 dB +/- 3 dB
- Type: Electret

Connectivity

- Cable length: 3 m
- Connector: 3.5 - 6.3 mm mono

Power

- Battery type: AA
- Battery voltage: 1.5 V
- Number of batteries: 1

Packaging dimensions

- Packaging dimensions (W x H x D):
14.7 x 24.7 x 7.4 cm
- Nett weight: 0.29 kg
- Gross weight: 0.59 kg

- Tare weight: 0.3 kg
- EAN: 87 10101 67951 8
- Number of products included: 1
- Packaging type: Carton

Outer Carton

- Outer carton (L x W x H): 55.5 x 47.5 x 39 cm
- Nett weight: 6.96 kg
- Gross weight: 15.5 kg
- Tare weight: 8.54 kg
- EAN: 87 10101 87411 1
- Number of consumer packagings: 24

Inner Carton

- Inner carton (L x W x H): 46 x 26.5 x 9 cm
- Nett weight: 0.65 kg
- Gross weight: 1.9 kg
- Tare weight: 1.25 kg
- EAN: 87 10101 87410 4
- Number of consumer packagings: 3

Highlights

Electret condenser

The sensitive electret condenser picks up every acoustic details for perfect sound reproduction and studio quality.

Low noise switch

You'll not hear any annoying 'clicks' when switching this microphone on and off.

Omni-directional design

This microphone's sensor is equally sensitive to sound from all directions.

Windshield

The integrated windshield prevents disturbing noises from wind gusts or breathing too close to the microphone.

5m microphone cable

Give yourself extra freedom of movement when using your microphone.

Die-cast metal alloy body

The tough metal body not only withstands rough handling, but also reduces resonance. The benefit is a longer operational life and a better reproduction.

Microphone storage box

The safe and convenient way to store your microphone and cable after use.

Table stand

This sturdy stand securely holds the microphone in place on any flat surface.

