



Philips  
Electret Microphone

SBCME570



## Studio quality

Liven up the occasion with an electret microphone for studio-quality recordings.

### Bring the occasion to life

- Electret condenser ensures studio quality sound and clarity
- Minimized noise when switching between on and off
- Omni-directional design picks up sound from all directions
- Windshield improves sound quality by preventing noise

### Always ready

- A 5m-long cable that's ideal for use with microphones
- Die-cast housing reduces resonance and extends product life
- Convenient box for microphone and cable storage
- Table stand allows hands-free use on a flat surface

# PHILIPS

# Specifications

## Sound

- Frequency response: 50 - 18 000 Hz
- Impedance: 600
- Polar pattern: Omni directional
- Sensitivity microphone: -45 dB +/- 3 dB
- Type: Electret

## Connectivity

- Cable length: 3 m
- Connector: 3.5 - 6.3 mm mono

## Power

- Battery type: AA
- Battery voltage: 1.5 V
- Number of batteries: 1

## Packaging dimensions

- Packaging dimensions (W x H x D):  
14.7 x 24.7 x 7.4 cm
- Nett weight: 0.29 kg
- Gross weight: 0.59 kg

- Tare weight: 0.3 kg
- EAN: 87 10101 67951 8
- Number of products included: 1
- Packaging type: Carton

## Outer Carton

- Outer carton (L x W x H): 55.5 x 47.5 x 39 cm
- Nett weight: 6.96 kg
- Gross weight: 15.5 kg
- Tare weight: 8.54 kg
- EAN: 87 10101 87411 1
- Number of consumer packagings: 24

## Inner Carton

- Inner carton (L x W x H): 46 x 26.5 x 9 cm
- Nett weight: 0.65 kg
- Gross weight: 1.9 kg
- Tare weight: 1.25 kg
- EAN: 87 10101 87410 4
- Number of consumer packagings: 3

# Highlights

## Electret condenser

The sensitive electret condenser picks up every acoustic details for perfect sound reproduction and studio quality.

## Low noise switch

You'll not hear any annoying 'clicks' when switching this microphone on and off.

## Omni-directional design

This microphone's sensor is equally sensitive to sound from all directions.

## Windshield

The integrated windshield prevents disturbing noises from wind gusts or breathing too close to the microphone.

## 5m microphone cable

Give yourself extra freedom of movement when using your microphone.

## Die-cast metal alloy body

The tough metal body not only withstands rough handling, but also reduces resonance. The benefit is a longer operational life and a better reproduction.

## Microphone storage box

The safe and convenient way to store your microphone and cable after use.

## Table stand

This sturdy stand securely holds the microphone in place on any flat surface.

