

Philips  
Baby Bottle Warmer



SBCSC215

## For home and car use special adapter included!

This bottle warmer is double insulated, it warms milk quickly to the ideal temperature and its handy car adapter means you can stick to regular feeding times, even on the move.

### **For use at home & away**

- Allows the appliance to be used in every car

### **Baby's food never too hot**

- Temperature control system maintains the ideal temperature
- Overheat protection stops baby's food ever getting too hot
- Uses the latest PTC heating technology for a safe product
- Double insulated for use anywhere in the home

### **Quick & easy food preparation**

- Fits every kind of bottle like oval, round and 'wide-necks'
- Short bottles and jars are easily lifted out
- Allows precise temperature setting at the required level.

**PHILIPS**

## Technical specifications

### Convenience

- Automatic power off
- Power on indication
- Ready indicator
- **Fits all bottles:** All baby bottles & jar types

### Accessories

- User manual

### Power

- **Mains power:** 220-240/12V car adapter
- **Power consumption:** 80/90 W

### Technical specifications

- **Heating time:** 8-15 minutes (home-car)
- **Safety classification:** Class 2

## Product highlights

### Car Adapter

A bottle warmer with car adapter that can heat baby's food in the car. This way you can maintain the feeding cycle and routine of your baby even while travelling.

### Temperature control system

The latest heating technology incorporates a PTC heating element and two sensors ensures the water in the beaker quickly reaches the ideal temperature and maintains it at a safe level that won't burn your baby's mouth with food or milk that is too hot.

### Overheat protection

To avoid the danger of accidentally burning your baby's mouth, the automatic switch off ensures the food does not get too hot.

### PTC heating element

The controlled heating process incorporating a PTC heating element and two sensors is ideal for consistently heating food and keeping it warm.

### Double insulation

With your safety and convenience in mind, the double insulated bottle warmer is designed to be used in every room in the house, not just where an earthed mains socket is available. There are no exposed metal parts that can become live.

### Fits all bottle and jar types

The product is designed in such a way that all kind of sizes and shapes of bottles and jars fit in.

### Bottle lifter

Even short bottles and jars are easily removed from the bottle warmer thanks to the handy lifting handle.

### Click-step temperature setting

With the Click-step temperature setting you can adjust the setting to suit the different types of food and bottles and jars you want to heat up.



Date of issue 2006-07-07

Version: 3.0

12 NC: 9082 100 00581  
EAN: 87 10101 68662 2

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.  
© 2006 Koninklijke Philips Electronics N.V.  
All Rights reserved.  
[www.philips.com](http://www.philips.com)