

# *baby monitor*

SBC **SC363**

- **Portable Parent unit**
- **Continuous Communication Link (pilot tone)**
- **Adjustable microphone sensitivity**
- **Power base included**
- **Two power adapters included**
- **Battery-low indicators**
- **Battery back-up option**
- **Two channels**

interference  
free

range up to  
**250m**

out-of-range  
indication



*Let's make things better.*



**PHILIPS**

# baby monitor

# SBC SC363

## Standard product information

### System information

- Power Supply 4x 1.5V, LR6/AA batteries for Baby unit (not included)  
4x 1.5V, LR6/AA batteries for Parent unit (not included)  
Power adapter DC 9V, 200mA (2x included)
- Battery operation time Up to 30 hours (Baby unit)  
Up to 12 hours (Parent unit)
- Operating voltage DC 9 Volt
- Transmission frequencies (/86&/87 version) Channel A 40.695 MHz  
Channel B 40.675 MHz
- Number of pilot tone codes 4
- Operating temperature 0° C to 40° C
- Storage temperature 0° C to 50° C
- Operating range Up to 250 meters (open air)
- Packaging content 1 x Baby unit  
1 x Parent unit  
1 x power base (Parent unit)  
2 x 9V AC/DC power adapter  
Instructions for use  
1 x carton packaging box (with flap)
- 12 NC /05U 9082 100 00447  
/86U 9082 100 00401  
/87U 9082 100 00402  
/13U 9082 100 00482  
/16U 9082 100 00483
- EAN / Barcode /05U 87 10101 67409 4  
/86U 87 10101 67315 8  
/87U 87 10101 67316 5  
/13U 87 10101 67673 9  
/16U 87 10101 67674 6

### Packaging information

- Type Corrugated carton window gift box
- Weight 1.14 kg
- Material 90% recycled
- Dimensions (cm) 24.0 x 8.2 x 30.5
- Languages packaging /86 English, French, German, Dutch  
/87 English, Spanish, Portuguese, Italian
- Languages IFU (12) English, French, Spanish, German, Dutch, Italian,  
Portuguese, Greek, Swedish, Norwegian, Finnish,  
Danish

### Outer carton

- Contents
- Dimensions (cm) 31.8x25.5x26.0
- Weight (gross) 3.9 kg
- EAN / Barcode /05U 87 10101 87304 6  
/13U 87 10101 87305 3  
/16U 87 10101 87306 0  
/86U 87 10101 87307 7  
/87U 87 10101 87308 4
- Country of origin China

*This Philips baby monitor lets you get on with your work or simply relax by yourself or with friends, secure in the knowledge that baby is resting peacefully or playing happily. Easy to install and use, this model features a high-quality speaker and microphone system that brings baby's voice close to you no matter where you are in the house.*

#### Interference free

*Advanced technology ensures no interference from other cordless devices or other brands of baby monitor.*

#### Range up to 250m

*Gives you the freedom to bring the Parent unit with you anywhere around the house.*

#### Out-of-range indication

*The Parent unit automatically checks that it is within range and alerts you if you go outside the reliable operational range.*

#### Portable Parent unit

*When powered on batteries, the Parent unit can be moved freely around the house.*

#### Adjustable microphone sensitivity

*The microphone's sensitivity can be adjusted to the level of sound you want to hear.*

#### Power base included

*For providing a constant power source to the Parent unit.*

#### Continuous Communication Link (pilot tone)

*Hidden signal that ensures a continuous link between both units so you only hear your baby's sounds.*

#### Two power adapters included

*For immediate operation of both units from the mains supply.*

#### Battery-low indicators

*Tell you immediately when your batteries are low.*

#### Battery back-up option

*Ensures operating reliability at all times.*

#### Two channels

*For reliable, interference-free operation.*

*Two AC power adapters included*

*Parent and Baby unit batteries optional*

Philips baby  care

*Let's make things better.*



**PHILIPS**