

PHILIPS

Baby Monitor

SBCSC363



Link check for more reliability

Wireless baby monitor that includes the unique feature of link check. This functionality checks if the communication link between baby and parent unit is working reliably.

Reliability & Piece of mind

- More transmission channels lowers the risk of interference
- Analog Pilot Tone minimizes interference from other devices
- System check ensures the monitor is working reliably
- System check alarm Informs of malfunction or out-of-range
- System check light reassures you that the monitor is working

Flexibility in monitoring your child

- Take the parent unit with you in and around the house
- Maximum operating distance between units with no obstacles

Convenience for you and your child

- Simplifies the selection of the volume you prefer
- High-quality microphone has adjustable sensitivity

Highlights

Number of channels

A choice of channels significantly reduces the risk of interference or sounds from other baby monitors in the neighbourhood.

Analogue Pilot Tone

A special tone that is transmitted along with the audio signal minimizes the chance of interference from other wireless appliances.

System check

When interference is detected in the communication link between the baby unit and parent unit or if the signal is too weak, the visual and audible alarms will be activated.

System check alarm

The parent unit gives an audible alarm when it is outside the communication range of the baby unit or when the communication link is not reliable.

System check light

Green light on the parent unit lights when the connection between the baby and the parent unit is reliable and flashes when the parent unit is outside the range of the baby unit or when the communication link is not reliable.

Use in & around the house

Rest assured that as you take the parent unit with you as you move in and around your house, the parent unit will stay in touch with the baby unit. It keeps you reassuringly informed and able to respond quickly when baby calls.

Range in open air

In the open air with no obstacles, the safe distance between the baby unit and parent unit is greater than indoors, so you can take the parent unit with you into the garden or to the neighbour's house without losing contact.

Volume control

A handy rotary control sets the volume to the ideal level to suit your preference.

Adjust Microphone sensitivity

Possibility to set the sensitivity of the microphone so you only hear the sounds you want to hear.

Specifications

Tuner/Reception/Transmission

Frequency band: 40.675 - 40.690 MHz

Number of pilot tones: 4

Pilot tone: Analogue

Maximum range: 250 m

Number of channels: 2

Convenience

Auto out-of-range warning

Battery low indication

Power on indication

System check: Battery check light

Volume control

Accessories

AC/DC Adaptor: 2x 9V DC 200mA

Batteries: 4 x AA baby unit not incl.

Belt clip: Belt clip on parent unit

Charger: Docking base for parent unit

User Manual

Power

Battery voltage: 4.8 V

Operating time on battery: 12 hr

