

baby monitor

SBC **SC365**

- **Sound-level lights**
- **Adjustable microphone sensitivity**
- **Continuous Communication Link (pilot tone)**
- **Out-of-range indication**
- **Charging base included**
- **Two power adapters included**
- **Battery-low indicators**
- **Battery back-up option**
- **Two channels**

interference free

range up to 250m

portable & rechargeable

in-range check



Let's make things better.



PHILIPS

baby monitor

SBC SC365

Standard product information

System information

- Power Supply 4x 1.5V, LR6/AA batteries for Baby unit (not included)
4x 1.2V, LR6/AA NiMH rechargeable batteries for Parent unit (included)
Power adapter DC 9V, 200mA (2x included)
- Battery operation time Up to 30 hours (Baby unit)
Up to 12 hours (Parent unit)
- Operating voltage DC 9 Volt
- Transmission frequencies (/86&/87 version) Channel A 40.695 MHz
Channel B 40.675 MHz
- Number of pilot tone codes 4
- Operating temperature 0° C to 40° C
- Storage temperature 0° C to 50° C
- Operating range Up to 250 meters (open air)
- Packaging content 1 x Baby unit
1 x Parent unit
1 x charging base (Parent unit)
2 x 9V AC/DC power adapter
4 x 1.2V, LR6/AA NiMH rechargeable batteries for Parent unit
Instructions for use
1 x carton packaging box with flap
- 12 NC /05U 9082 100 00448
/86U 9082 100 00405
/87U 9082 100 00406
/13U 9082 100 00484
/16U 9082 100 00485
- EAN / Barcode /05U 87 10101 67410 0
/86U 87 10101 67319 6
/87U 87 10101 67320 2
/13U 87 10101 67675 3
/16U 87 10101 67676 0

Packaging information

- Type Corrugated carton window gift box
- Weight 1.14 kg
- Material 90% recycled
- Dimensions (cm) 24.0 x 8.2 x 30.5
- Languages packaging /86 English, French, German, Dutch
/87 English, Spanish, Portuguese, Italian
- Languages IFU (12) English, French, Spanish, German, Dutch, Italian,
Portuguese, Greek, Swedish, Norwegian, Finnish,
Danish

Outer carton

- Contents 3
- Dimensions (cm) 31.8x25.5x26.0
- Weight (gross) 3.9 kg
- EAN / Barcode /05U 87 10101 87309 1
/13U 87 10101 87310 7
/16U 87 10101 87311 4
/86U 87 10101 87312 1
/87U 87 10101 87313 8
- Country of origin China

This Philips baby monitor lets you get on with your work or simply relax by yourself or with friends, secure in the knowledge that baby is resting peacefully or playing happily. Easy to install and use, this model features sound level lights that enable you to watch the level of baby's sounds without disturbance, no matter where you are in the house.

Interference free

Advanced technology ensures no interference from other cordless devices or other brands of baby monitor.

Range up to 250m

Gives you the freedom to bring the Parent unit with you anywhere around the house.

Portable and rechargeable

Cost-saving rechargeable batteries in the Parent unit last up to 12 hours before recharging is needed.

In-range check

The Link light lights continuously when everything is O.K., and emits an audio and visual alarm if you go outside the operational range.

Sound-level lights

Let you watch the level of the baby's sounds with the volume turned down.

Adjustable microphone sensitivity

The microphone's sensitivity can be adjusted to the level of sound you want to hear.

Continuous Communication Link (pilot tone)

Hidden signal that ensures a continuous link between both units so you only hear your baby's sounds.

Out-of-range indication

The Parent unit automatically checks that it is within range and alerts you if you go outside the reliable operational range.

Charging base included

For quick and easy charging of the batteries.

Two power adapters included

For immediate operation of both units from the mains supply.

Battery-low indicators

Tell you immediately when your batteries are low.

Battery back-up option

Ensures operating reliability at all times.

Two channels

For reliable, interference-free operation.

Two AC power adapters included.

Rechargeable batteries for Parent unit included.

Baby unit batteries optional.

Philips baby  care

Let's make things better.



PHILIPS