

PHILIPS

Baby Monitor

SBCSC365



Baby monitor with sound level lights

This baby monitor is easy to install and use, this model features sound level lights that enable you to watch the level of baby's sounds without disturbance, no matter where you are in the house.

Convenience for you and your child

- Charging Base keeps batteries recharged and ready for use
- Simplifies the selection of the volume you prefer
- Sound-level lights display the level of your baby's sounds
- High-quality microphone has adjustable sensitivity
- Save money with rechargeable parent unit and charging base

Reliability & Piece of mind

- More transmission channels lowers the risk of interference
- Battery low indication shows when to refresh batteries
- System check alarm Informs of malfunction or out-of-range
- System check light reassures you that the monitor is working
- Free from interference from other cordless devices
- Analog Pilot Tone minimizes interference from other devices

Flexibility in monitoring your child

- Take the parent unit with you in and around the house

Highlights

Charging base

Thanks to the built-in battery charger in the base, you get extra freedom (when fully charged) to take the parent unit with you around the home and stay in touch with your baby. It's also a convenient place to store the parent unit, and ensure it's always ready for use.

Volume control

A handy rotary control sets the volume to the ideal level to suit your preference.

Sound-level lights

Sometimes it's a great help to 'see' when your baby makes a sound. This row of lights provide you with a clear visual indication.

Adjust Microphone sensitivity

Possibility to set the sensitivity of the microphone so you only hear the sounds you want to hear.

Rechargeable Parent unit

Putting the parent unit on the charging base will automatically start recharging of the batteries, so it's always ready for portable use.

Number of channels

A choice of channels significantly reduces the risk of interference or sounds from other baby monitors in the neighbourhood.

Battery-low indication

To know in time when the batteries need to be recharged or replaced.

System check alarm

The parent unit gives an audible alarm when it is outside the communication range of the baby unit or when the communication link is not reliable.

System check light

Green light on the parent unit lights when the connection between the baby and the parent unit is reliable and flashes when the parent unit is outside the range of the baby unit or when the communication link is not reliable.

Interference free

To ensure that you stay in contact with your baby, the link between parent unit and baby unit incorporates technology that shuts out unwanted noise and signals from other cordless devices. You only hear your baby.

Analogue Pilot Tone

A special tone that is transmitted along with the audio signal minimizes the chance of interference from other wireless appliances.

Use in & around the house

Rest assured that as you take the parent unit with you as you move in and around your house, the parent unit will stay in touch with the baby unit. It keeps you reassuringly informed and able to respond quickly when baby calls.

Range in open air

In the open air with no obstacles, the safe distance between the baby unit and parent unit is greater than indoors, so you can take the parent unit with you into the garden or to the neighbour's house without losing contact.

Specifications

Tuner/Reception/Transmission

Frequency band: 40.675 - 40.690 MHz

Number of pilot tones: 4

Pilot tone: Analogue

Maximum range: 250 m

Number of channels: 2

Convenience

Auto out-of-range warning

Battery charging indication

Battery low indication

Power on indication

Sound-level lights

System check: Battery check light

Volume control

Accessories

AC/DC Adaptor: 2x 9V DC 200mA

Batteries: 4 x AA baby unit not incl.

Belt clip: Belt clip on parent unit

Charger: Charging base for parent unit

User Manual

Power

Battery voltage: 4.8 V

Operating time on battery: 12 hr

