


baby monitor

SBC SC368

- **Adjustable microphone sensitivity**
- **Continuous Communication Link (pilot tone)**
- **Out-of-range indication**
- **Charging base included**
- **Two power adapters included**
- **Battery-low indicators**
- **Battery back-up option**
- **Two channels**

- **ultra-compact parent unit**
- **interference free**
- **range up to 250m**
- **portable & rechargeable**
- **in-range check**



Let's make things better.



PHILIPS

baby monitor

SBC SC368

Standard product information

System information

- Power Supply 4x 1.5V, LR6/AA batteries for Baby unit (not included)
3.6V 550mAh NiMH rechargeable battery pack (included)
Power adapter DC 9V, 200mA (2x included)
- Battery operation time Up to 30 hours (Baby unit)
Up to 12 hours (Parent unit)
- Operating voltage DC 9 Volt
- Transmission frequencies (/86&/87 version) Channel A 40.695 MHz
Channel B 40.675 MHz
- Number of pilot tone codes 4
- Operating temperature 0° C to 40° C
- Storage temperature 0° C to 50° C
- Operating range Up to 250 meters (open air)
- Packaging content 1 x Baby unit
1 x Parent unit
1 x charging base
2 x 9V AC/DC power adapter
3.6V 550mAh NiMH rechargeable battery pack (included)
Instructions for use
1 x carton packaging box
- 12 NC /13U 9082 100 00487
/16U 9082 100 00488
/86U 9082 100 00409
/87U 9082 100 00411
- EAN / Barcode /13U 87 10101 67678 4
/16U 87 10101 67679 1
/86U 87 10101 67325 7
/87U 87 10101 67324 0

Packaging information

- Type Corrugated carton window gift box
- Weight 0.95 kg
- Material 90% recycled
- Dimensions (cm) 24.0 x 8.2 x 30.5
- Languages packaging /86 English, French, German, Dutch
/87 English, Spanish, Portuguese, Italian
- Languages IFU (12) English, French, Spanish, German, Dutch, Italian,
Portuguese, Greek, Swedish, Norwegian, Finnish,
Danish
- Outer carton
- Contents 3
- Dimensions (cm) 31.8x25.5x26.0
- Weight (gross) 3.33 kg
- EAN / Barcode /13U 87 10101 87217 6
/16U 87 10101 87318 3
/86U 87 10101 87319 0
/87U 87 10101 87320 6

This Philips baby monitor lets you get on with your work or simply relax by yourself or with friends, secure in the knowledge that baby is resting peacefully or playing happily. Easy to install and use, this model features an ultra-compact Parent unit that you can clip onto your belt so you can easily move around the house and still always hear baby.

Ultra-compact Parent unit

Provides clip-on convenience for maximum portability around the house.

Interference free

Advanced technology ensures no interference from other cordless devices or other brands of baby monitor.

Range up to 250m

Gives you the freedom to bring the Parent unit with you anywhere around the house.

Portable and rechargeable

Rechargeable batteries in the Parent unit last up to 12 hours before recharging is needed.

In-range check

The Link light lights continuously when everything is O.K. and emits an audio and visual alarm if you go outside the operational range.

Adjustable microphone sensitivity

The microphone's sensitivity can be adjusted to the level of sound you want to hear.

Continuous Communication Link (pilot tone)

Hidden signal that ensures a continuous link between both units so you only hear your baby's sounds.

Out-of-range indication

The Parent unit automatically checks that it is within range and alerts you if you go outside the reliable operational range.

Charging base included

For quick and easy charging of the batteries.

Two power adapters included

For immediate operation of both units from the mains supply.

Battery-low indicators

Tell you immediately when your batteries are low.

Battery back-up option

Ensures operating reliability at all times.

Two channels

For reliable, interference-free operation.

Two AC power adapters included.

Rechargeable batteries for Parent unit included.

Baby unit batteries optional.

Philips baby  care

Let's make things better.



PHILIPS