

PHILIPS

Family Baby
Monitor

SBCSC369



Two parent units!

Baby monitor with two parent units for freedom of movement without losing contact with your baby. All units are fully portable. Keep in touch with your baby from up to 200 m away.

Reliability & Piece of mind

- More transmission channels lowers the risk of interference
- Analog Pilot Tone minimizes interference from other devices
- Battery low indication shows when to refresh batteries
- System check ensures the monitor is working reliably
- System check alarm Informs of malfunction or out-of-range
- System check light reassures you that the monitor is working

Flexibility in monitoring your child

- Take the parent unit with you in and around the house
- Maximum operating distance between units with no obstacles

Convenience for you and your child

- Charging Base keeps batteries recharged and ready for use
- Simplifies the selection of the volume you prefer
- Save money with rechargeable parent unit and charging base

Extra portability

Highlights

Number of channels

A choice of channels significantly reduces the risk of interference or sounds from other baby monitors in the neighbourhood.

Analogue Pilot Tone

A special tone that is transmitted along with the audio signal minimizes the chance of interference from other wireless appliances.

Battery-low indication

To know in time when the batteries need to be recharged or replaced.

System check

When interference is detected in the communication link between the baby unit and parent unit or if the signal is too weak, the visual and audible alarms will be activated.

System check alarm

The parent unit gives an audible alarm when it is outside the communication range of the baby unit or when the communication link is not reliable.

System check light

Green light on the parent unit lights when the connection between the baby and the parent unit is reliable and flashes when the parent unit is outside the range of the baby unit or when the communication link is not reliable.

Use in & around the house

Rest assured that as you take the parent unit with you as you move in and around your house, the parent unit will stay in touch with

the baby unit. It keeps you reassuringly informed and able to respond quickly when baby calls.

Range in open air

In the open air with no obstacles, the safe distance between the baby unit and parent unit is greater than indoors, so you can take the parent unit with you into the garden or to the neighbour's house without losing contact.

Charging base

Thanks to the built-in battery charger in the base, you get extra freedom (when fully charged) to take the parent unit with you around the home and stay in touch with your baby. It's also a convenient place to store the parent unit, and ensure it's always ready for use.

Volume control

A handy rotary control sets the volume to the ideal level to suit your preference.

Rechargeable Parent unit

Putting the parent unit on the charging base will automatically start recharging of the batteries, so it's always ready for portable use.

Sound-level lights

Sometimes it's a great help to 'see' when your baby makes a sound. This row of lights provide you with a clear visual indication.

Extra small Parent unit

The parent unit is very small, so that you can put it easily in your pocket or clip it to your belt. Easy to take with you when you move around the house.

Specifications

Tuner/Reception/Transmission

Frequency band: 49.830 - 49.890 MHz

Number of pilot tones: 4

Pilot tone: Analogue

Maximum range: 200 m

Number of channels: 2

Convenience

Auto out-of-range warning

Battery charging indication

Battery low indication

Power on indication

Sound-level lights

System check: Battery check light, System check alarm, System check light

Volume control

Accessories

AC/DC Adaptor: 3x 9V DC 200mA

Batteries: 4 x AA baby unit not incl.

Belt clip: Belt clip on parent unit

User Manual

Power

Operating time on battery: 12 hr

