

# PHILIPS

Baby Monitor

SBCSC466



## Both units rechargeable

Both baby unit and parent unit of the baby monitor have rechargeable batteries.

### Reliability & Piece of mind

- More transmission channels lowers the risk of interference
- Battery low indication shows when to refresh batteries
- Digital Pilot Tone minimizes interference from other devices
- System check ensures the monitor is working reliably
- System check alarm Informs of malfunction or out-of-range
- System check light reassures you that the monitor is working

### Convenience for you and your child

- Charging Base keeps batteries recharged and ready for use
- Simplifies the selection of the volume you prefer
- Sound-level lights display the level of your baby's sounds
- High-quality microphone has adjustable sensitivity
- Save money with rechargeable parent unit and charging base

### Flexibility in monitoring your child

### Comforting your baby

# Highlights

## Number of channels

A choice of channels significantly reduces the risk of interference or sounds from other baby monitors in the neighbourhood.

## Battery-low indication

To know in time when the batteries need to be recharged or replaced.

## Digital Pilot Tone

A special tone that is transmitted along with the audio signal to minimize the chance of interference from other wireless appliances.

## System check

When interference is detected in the communication link between the baby unit and parent unit or if the signal is too weak, the visual and audible alarms will be activated.

## System check alarm

The parent unit gives an audible alarm when it is outside the communication range of the baby unit or when the communication link is not reliable.

## System check light

Green light on the parent unit lights when the connection between the baby and the parent unit is reliable and flashes when the parent unit is outside the range of the baby unit or when the communication link is not reliable.

## Charging base

Thanks to the built-in battery charger in the base, you get extra freedom (when fully charged) to take the parent unit with you around the home and stay in touch with your baby. It's also a convenient place to store the parent unit, and ensure it's always ready for use.

## Volume control

A handy rotary control sets the volume to the ideal level to suit your preference.

## Sound-level lights

Sometimes it's a great help to 'see' when your baby makes a sound. This row of lights provide you with a clear visual indication.

## Adjust Microphone sensitivity

Possibility to set the sensitivity of the microphone so you only hear the sounds you want to hear.

## Rechargeable Parent unit

Putting the parent unit on the charging base will automatically start recharging of the batteries, so it's always ready for portable use.

## Use in & around the house

Rest assured that as you take the parent unit with you as you move in and around your house, the parent unit will stay in touch with the baby unit. It keeps you reassuringly informed and able to respond quickly when baby calls.

## Range in open air

In the open air with no obstacles, the safe distance between the baby unit and parent unit is greater than indoors, so you can take the parent unit with you into the garden or to the neighbour's house without losing contact.

## Night light

A soft, glowing light is reassuring and provides a focal point in the dark.

# Specifications

## Tuner/Reception/Transmission

Frequency band: 40.675 - 40.690 MHz

Number of pilot tones: 16

Pilot tone: Digital

Maximum range: 250 m

Number of channels: 4

## Convenience

Auto out-of-range warning

Battery charging indication

Battery low indication

Power on indication

Volume control

## Accessories

AC/DC Adaptor: 2x 9V DC 200mA

Batteries: NiMH pack for Baby unit incl

User Manual

## Power

Battery voltage: 4.8 V

Operating time on battery: 12 hr

