

# PHILIPS

## Baby Monitor

SBCSC468



## Extra small parent unit with belt clip

Extra small parent unit is easily carried when moving around. Freedom of movement without losing contact with your baby.

### Extra portability

- Take the parent unit with you in and around the house
- Extra small Parent unit is easily carried when moving around

### Reliability & Piece of mind

- More transmission channels lowers the risk of interference
- Battery low indication shows when to refresh batteries
- Digital Pilot Tone minimizes interference from other devices
- Digital System Check ensures the monitor is working reliably

### Convenience for you and your child

- Charging Base keeps batteries recharged and ready for use
- Simplifies the selection of the volume you prefer
- Sound-level lights display the level of your baby's sounds

### Flexibility in monitoring your child

### Comforting your baby

# Highlights

## Use in & around the house

Rest assured that as you take the parent unit with you as you move in and around your house, the parent unit will stay in touch with the baby unit. It keeps you reassuringly informed and able to respond quickly when baby calls.

## Extra small Parent unit

The parent unit is very small, so that you can put it easily in your pocket or clip it to your belt. Easy to take with you when you move around the house.

## Number of channels

A choice of channels significantly reduces the risk of interference or sounds from other baby monitors in the neighbourhood.

## Battery-low indication

To know in time when the batteries need to be recharged or replaced.

## Digital Pilot Tone

A special tone that is transmitted along with the audio signal to minimize the chance of interference from other wireless appliances.

## Digital System check

A visible and audible warning is activated if the communication link between the baby unit and parent unit is unreliable.

## Charging base

Thanks to the built-in battery charger in the base, you get extra freedom (when fully charged) to take the parent unit with you

around the home and stay in touch with your baby. It's also a convenient place to store the parent unit, and ensure it's always ready for use.

## Volume control

A handy rotary control sets the volume to the ideal level to suit your preference.

## Sound-level lights

Sometimes it's a great help to 'see' when your baby makes a sound. This row of lights provide you with a clear visual indication.

## Adjust Microphone sensitivity

Possibility to set the sensitivity of the microphone so you only hear the sounds you want to hear.

## Rechargeable Parent unit

Putting the parent unit on the charging base will automatically start recharging of the batteries, so it's always ready for portable use.

## Range in open air

In the open air with no obstacles, the safe distance between the baby unit and parent unit is greater than indoors, so you can take the parent unit with you into the garden or to the neighbour's house without losing contact.

## Night light

A soft, glowing light is reassuring and provides a focal point in the dark.

# Specifications

## Tuner/Reception/Transmission

Frequency band: 40.675 - 40.690 MHz

Number of pilot tones: 16

Pilot tone: Digital

Maximum range: 200 m

Number of channels: 4

## Convenience

Auto out-of-range warning

Battery charging indication

Battery low indication

Power on indication

Volume control

## Accessories

AC/DC Adaptor: 2x 9V DC 200mA

Batteries: 4 x AA baby unit not incl.

Belt clip: Belt clip on parent unit

User Manual

## Power

Battery voltage: 4.8 V

Operating time on battery: 12 hr

