

PHILIPS

Baby Cam

SBCSC490



Colour baby cam and baby monitor in one

Wireless colour baby cam and baby monitor in one

Watch & hear your baby

- See your baby on TV in full color with baby cam
- Night vision to see your baby even in a dark room
- Record your baby during its early years on DVD or VCR

Reliability & Piece of mind

- More transmission channels lowers the risk of interference
- Digital System Check ensures the monitor is working reliably
- System check alarm Informs of malfunction or out-of-range
- System check light reassures you that the monitor is working
- Battery low indication shows when to refresh batteries

Convenience for you and your child

- Sound-level lights display the level of your baby's sounds
- Save money with rechargeable parent unit and charging base
- Charging Base keeps batteries recharged and ready for use

Flexibility in monitoring your child

Highlights

Colour baby cam

Natural looking, real-life colour images of your baby are not just reassuring and natural but fun to look at or record as memories to treasure.

Night vision

When your baby's room gets darker, the camera automatically switches over to night vision so you can still see every reassuring detail without turning on the lights. In the dark you can't see colours so the video is transmitted as sharp black and white images.

Record baby on DVD+RW

To capture precious moments in your baby's natural development and keep them as treasured memories on a DVD recorder or VCR, simply use your Baby Cam like a video camera. And because baby is totally unaware of being recorded, you'll capture the most natural behaviour.

Number of channels

A choice of channels significantly reduces the risk of interference or sounds from other baby monitors in the neighbourhood.

Digital System check

A visible and audible warning is activated if the communication link between the baby unit and parent unit is unreliable.

System check alarm

The parent unit gives an audible alarm when it is outside the communication range of the baby unit or when the communication link is not reliable.

System check light

Green light on the parent unit lights when the connection between the baby and the parent unit is reliable and flashes when the parent unit is outside the range of the baby unit or when the communication link is not reliable.

Battery-low indication

To know in time when the batteries need to be recharged or replaced.

Sound-level lights

Sometimes it's a great help to 'see' when your baby makes a sound. This row of lights provide you with a clear visual indication.

Rechargeable Parent unit

Putting the parent unit on the charging base will automatically start recharging of the batteries, so it's always ready for portable use.

Charging base

Thanks to the built-in battery charger in the base, you get extra freedom (when fully charged) to take the parent unit with you around the home and stay in touch with your baby. It's also a convenient place to store the parent unit, and ensure it's always ready for use.

Volume control

A handy rotary control sets the volume to the ideal level to suit your preference.

Adjust Microphone sensitivity

Possibility to set the sensitivity of the microphone so you only hear the sounds you want to hear.

Use in & around the house

Rest assured that as you take the parent unit with you as you move in and around your house, the parent unit will stay in touch with the baby unit. It keeps you reassuringly informed and able to respond quickly when baby calls.

Specifications

Tuner/Reception/Transmission

Frequency band: 2.4GHz
Number of channels: 4

Convenience

Auto out-of-range warning
Battery charging indication
Battery full indication
Battery low indication
System check: Battery check light, System check alarm, System check light

Accessories

AC/DC Adaptor: 2x 12V DC 500 mA
Batteries: 6 x AA baby unit not incl.
Cables: RCA Audio & Video cable
Charger: Docking base for parent unit
Extension cable: RCA to SCART converter
User Manual
Battery pack: NiMH pack parent unit incl.

Power

Charging time: 12 hr
Operating time on battery: 5 hr
Power supply: AC/DC Adapter

Technical specifications

Operating temperature range: 0 .. 40 °C

