



Philips  
TV antenna

**UHF/VHF/FM**

Indoor  
42 dB amplified

**SBCTT950**



## Receive analog and digital TV

with this 42 dB amplified antenna

This unique antenna is motorized to conveniently remotely adjust position of the dipoles and UHF element over 100 degrees for optimum reception. Works with any remote control.

### **Enjoy more programming choices**

- 42 dB amplification
- External antenna switch

### **Improve your picture quality**

- Low noise amplification maintains signal quality
- Rotary gain control to adjust amplification

### **Easy to position**

- Weighted base for excellent physical stability
- Optional DC 12V power source

### **Sleek, contemporary styling**

- Sleek design lines compliment today's new TVs
- Compact design fits virtually anywhere

# PHILIPS

TV antenna  
UHF/VHF/FM Indoor, 42 dB amplified

# Specifications

## Technical specifications

- Safety standards: According to EN 60065
- EMC standards: According to EN 89/336/EEC

## Tuner/Reception/Transmission

- Aerial Output: 75 ohm coaxial (IEC75)
- Antenna type: Telescopic, Spiral Loop
- Tuner bands: UHF, VHF
- Gain (antenna + amplifier): 42 dB

## Power

- On/Off switch
- Mains power: 12V DC
- Power consumption: 5mA W

## Accessories

- User Manual

SBC TT950/00

# Highlights

## 42 dB Amplification

42 dB amplification boosts weak signals, expanding your reception range and allowing you to receive more signals over a greater distance.

## External Antenna Switch

Internal/external antenna switch allows you to easily switch between your external antenna and your cable system for more programming choices.

## Low noise amplification

Together with the adjustable amplification, low noise amplification ensures you of a great reception range and improves the quality of your signal.

## Rotary gain control

The rotary gain control allows you to easily adjust the antenna's amplification for optimum reception.

## Weighted base

The weighted base stabilizes the antenna's position so you enjoy more positioning choices.

## Optional DC 12V power source

Optional DC 12V power source allows you to choose to plug antenna into your vehicle's cigarette lighter.

## Design lines compliment TVs

Simple, elegant design lines compliment today's new TVs.

## Compact design

Compact design allows you to position the antenna virtually anywhere.



Issue date 2014-02-05

Version: 5.1.7

12 NC: 9082 100 02095  
EAN: 87 10895 78021 6

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)