

# PHILIPS

# AVENT

DECT baby monitor

SCD496/00



## Guaranteed zero interference

### With DECT digital technology

This digital technology provides a secured, private connection, because you want to be the only one listening to your baby. Automatically chooses an unused channel and switches as it detects another device using the same channel. .

#### **Complete peace of mind**

- Guarantees zero interference from any other device
- Indicates a continuous connection between the two units
- Uses lights to indicate if the baby makes noise

#### **Mobility in and around the house**

- The belt clip provides hands-free convenience and mobility
- Small, mobile parent unit to freely roam around the house
- 300 m range ensures secure reception in and around the house

#### **Soothing words**

- Provides the ability to allow you to talk to the baby


# Highlights

## Guaranteed zero interference



Guarantees zero interference from any other device (other baby monitors, cordless phones and cell phones). Provides a secure and private connection using data encryption. You will be the only one who can hear your baby and you only hear your own baby.

## Digital signal confirmation



Indicates a continuous connection between the baby and the parent unit with visible and audible link indicators.

## Sound level lights

Uses lights to indicate if the baby makes noise, even with volume off.

## Small, mobile parent unit



Allows you to freely roam around the house due to the small size, but still hear when your baby needs you.

## Belt clip



The belt clip provides hands-free convenience and mobility.

## With a range up to 300 m

With a range up to 300 m you are ensured a secure reception in and around the house.

## Parent talkback

Provides the ability to allow you to hear the baby and talk to the baby.

# Specifications

## Technical specifications

Operating temperature range: 0 .. 40 °C  
Storage temperature range: -20 .. +60 °C

## Tuner/Reception/Transmission

Frequency band: DECT  
Automatic channel selection  
Number of channels: 120

## Convenience

Auto out-of-range warning  
Battery low indication  
Power on indication  
Sound-level lights  
System check: Battery check light, System check alarm, System check light  
Volume control

## Accessories

AC/DC adaptor: 2x 9VDC, 300mA  
Belt clip  
DFU/ user manual: Dutch, English, Finnish, French, German, Greek, Italian, Portuguese, Spanish, Swedish, Norwegian, Danish  
Quick start guide

## Power

Power supply: 230-240 V

## Logistic data

EAN F-box  
F-box dimensions (W x H x D):  
220x187x94 mm

## Development stages

Stage: 0 - 6 months, 6 - 12 months

