

# PHILIPS

# AVENT

## DECT Baby Monitor

SCD497/00



## Guaranteed zero interference

### With DECT digital technology

This digital technology provides a secured, private connection, because you want to be the only one listening to your baby. Automatically chooses an unused channel and switches as it detects another device using the same channel.

#### **Complete peace of mind**

- Guarantees zero interference from any other device
- Indicates a continuous connection between the two units
- Uses lights to indicate if the baby makes a noise

#### **Mobility in and around the house**

- Rechargeable parent unit for minimum 24 hours of monitoring
- The belt clip provides hands-free convenience and mobility
- Small, mobile parent unit to freely roam around the house
- 300-m range ensures secure reception in and around the house

#### **Soothing sights and words**

- Comforts the baby in the dark with soothing stars
- Allows you to talk to the baby


# Highlights

## Guaranteed zero interference



Guarantees zero interference from any other device (other baby monitors, cordless phones and mobile phones). Provides a secure and private connection using data encryption. You will be the only one who can hear your baby and you will only hear your own baby.

## Digital signal confirmation



Indicates a continuous connection between the baby and the parent unit with visible and audible link indicators.

## Sound level lights

Uses lights to indicate if the baby makes a noise, even with volume off.

## Rechargeable parent unit




The rechargeable parent unit gives you a minimum of 24 hours of cordless monitoring with a range of up to 300 m (900 feet).

## Small, mobile parent unit



Allows you to freely roam around the house due to the small size, but still hear when your baby needs you.

## Belt clip



The belt clip provides hands-free convenience and mobility.

## With a range of up to 300 m

With a range of up to 300 m you are assured of a secure reception in and around the house.

## Starry night-light

Nightlight with soothing stars to comfort your baby.

## Parent talkback

Allows you to hear the baby and talk to the baby.

# Specifications

## Technical specifications

Operating temperature range: 0–40 °C  
Storage temperature range: –20–+60 °C

## Tuner/Reception/Transmission

Frequency band: DECT  
Automatic channel selection  
Number of channels: 120

## Convenience

Auto out-of-range warning  
Battery charging indication  
Battery low indication  
Night light  
Power on indication  
Sound-level lights  
System check: Battery check light, System check alarm, System check light  
Volume control

## Accessories

AC/DC adapter: 2 x 9 VDC, 300 mA  
Batteries: 2 x AAA NiMH rechargeable  
Belt clip  
DFU/user manual: Dutch, English, Finnish, French, German, Greek, Italian, Portuguese, Spanish, Swedish, Norwegian, Danish  
Quick start guide

## Power

Charging time: 8 hrs  
Power supply: 230–240 V  
Rechargeable  
Operating time on battery: 24 hour(s)

## Logistic data

EAN F-box  
F-box dimensions (W x H x D): 220 x 187 x 94 mm

## Development stages

Stages: 0–6 months, 6–12 months

