

PHILIPS

AVENT

DECT Baby Monitor

SCD498/00



Guaranteed zero interference

With DECT digital technology

This digital technology provides a secure, private connection, because you want to be the only one listening to your baby. Automatically chooses an unused channel and switches if it detects another device using the same channel.

Complete peace of mind

- Guarantees zero interference from any other device
- Indicates a continuous connection between the two units
- Uses lights to indicate if the baby makes a noise

Ultimate mobility in and around the house

- Travel pouch for easy storage
- Belt clip and neck cord for hands-free convenience
- Rechargeable parent unit for minimum 24 hours of monitoring
- Small, mobile parent unit to freely roam around the house
- 300-m range ensures secure reception in and around the house

Soothing sights and words

- Comforts the baby in the dark with soothing stars
- Allows you to talk to the baby

Highlights

Guaranteed zero interference



Guarantees zero interference from any other device (other baby monitors, cordless phones and mobile phones). Provides a secure and private connection using data encryption. You will be the only one who can hear your baby and you will only hear your own baby.

Digital signal confirmation



Indicates a continuous connection between the baby and the parent unit with visible and audible link indicators.

Sound level lights

Uses lights to indicate if the baby makes a noise, even with volume off.

Travel pouch

Travel pouch for easy storage while travelling.

Belt clip and neck cord

The belt clip and neck cord provide hands-free convenience and mobility: clip the parent unit to your belt or wear it around your neck.

Small, mobile parent unit



Allows you to freely roam around the house due to the small size, but still hear when your baby needs you.

With a range of up to 300 m

With a range of up to 300 m you are assured of a secure reception in and around the house.

Starry night-light

Nightlight with soothing stars to comfort your baby.

Parent talkback

Allows you to hear the baby and talk to the baby.

Specifications

Technical specifications

Operating temperature range: 0–40 °C
Storage temperature range: –20–+60 °C

Tuner/Reception/Transmission

Frequency band: DECT
Automatic channel selection
Number of channels: 120

Convenience

Auto out of range warning
Battery charging indication
Battery low indication
Night light
Power on indication
Sound-level lights
System check: Battery check light, System check alarm, System check light
Volume control

Accessories

AC/DC adapter: 2 x 9 VDC, 300 mA
Batteries: 2 x AAA NiMH rechargeable
Belt clip
Charger: Charging base for parent unit
DFU/user manual: Dutch, English, Finnish, French, German, Greek, Italian, Portuguese, Spanish, Swedish, Norwegian, Danish
Quick start guide

Power

Charging time: 8 hour(s)
Power supply: 230–240 V
Rechargeable
Operating time on battery: 24 hour(s)

Logistic data

EAN F-box
F-box dimensions (W x H x D): 305 x 187 x 135 mm

Development stages

Stages: 0–6 months, 6–12 months

