

Highlights

Zero interference with DECT

DECT technology guarantees zero interference from any other transmitting product like other baby monitors, cordless phones and cell phones. Data encryption provides a secure and private connection, so you can be sure that you are the only one that can hear your baby.

Perfect clear sound


Hear every tiny giggle, gurgle, and hic-up with perfect clarity. DECT (Digital Enhanced Cordless Telecommunications) technology provides high quality, crystal clear sound so you can hear your baby anytime.

Smart ECO mode




The unique Smart ECO mode automatically minimizes your transmission power and increases your battery lifetime. The closer you are to your baby, the less power is needed for a perfect connection (not available in US and Canada).

Always connected



The parent unit will alert you when your monitor is out of range or when the power is low, helping you make sure that you are always connected to your baby.

Sound activation 5 LED lights




Lights are activated to indicate the level of sound in your baby's room. Even when the Parent Unit is muted.

300m Range



Indoor range up to 50 meters*, Outdoor range up to 300 meters*.

Battery and mains operated



The parent unit runs perfectly on mains power. For extra mobility you can also insert batteries to allow cordless use of the parent unit. You can insert two 1.5V R6 AA alkaline non-rechargeable batteries or two 1.2V R6 AA rechargeable batteries.

Operating time up to 24 hours



The small parent unit will give you the freedom of cordless streaming for up to 24 hours before re-charging is required. However this is depending on the type of batteries used and how often and how long you use the parent unit on batteries.

Comforting nightlight

Your baby may still be restless when you first put them to bed. Help soothe and calm your baby to sleep with the warm tranquil glow of the nightlight.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Features

DECT Technology
Energy saving Smart ECO mode
Linked and in range indication
Sound activation lights: 5 LED lights
Volume control and sound activation
Comforting night light
Indoor range up to: 50m
Outdoor range up to: 300 meters

Power

Operating time on battery hour: 24 hours
Power Supply: 120 V (US), 220 - 240 V

Tuner/Reception/Transmission

Frequency band: DECT
Automatic channel selection
Number of channels: 120

Convenience

Battery low indication
Volume control
Auto out-of-range warning
Sound-level lights

Technical specifications

Operating temperature range °C: 10 - 40 °C
Storage temperature range: 10 - 40 °C

Logistic data

F-box dimensions (W x H x D): 220 x 156 x 56 mm

Development stages

Stages: Pregnancy, 0 - 6 months

Accessories

Quick start guide
User manual

