

Highlights

Zero interference with DECT



DECT technology guarantees zero interference from any other transmitting products like other baby monitors, cordless phones and mobile phones. Data encryption provides a secure and private connection, so you can be sure that you are the only one that can hear your baby.

Perfect clear sound



Hear every tiny giggle, gurgle and hiccup with perfect clarity. DECT (Digital Enhanced Cordless Telecommunications) technology provides high quality, crystal clear sound so you can hear your baby all the time.

ECO mode



Switch on the ECO mode to reduce transmission power in the baby's room. In ECO mode, the units only connect when the baby makes a sound.

Sound activation 5 LED lights



Lights are activated to indicate the level of sound in your baby's room, even when the Parent Unit is muted.

Always connected



The parent unit will alert you when your monitor is out of range or when the power is low, helping you to make sure that you are always connected to your baby.

330 m Range



Indoor range up to 50 metres*. Outdoor range up to 330 metres*.

Rechargeable parent unit



The rechargeable parent unit enables you to move in and around the home.

Operating time up to 24 hours



The small, rechargeable parent unit will give you the freedom of cordless streaming for up to 24 hours. However, this depends on the type of batteries used and how often and how long you use the parent unit powered by the batteries.

Calming and soothing

Help soothe your baby to sleep with the warm tranquil glow of the night light and soft lullabies.

Talk back function



Sometimes all your baby needs is the soothing sound of your voice. With one click of this essential feature, you can connect with your baby from anywhere around the home.

Specifications

Power

Operating time on battery hour(s): 24 hour(s)
Power Supply: 120 V (US), 220–240 V
Charging time: 8 hour(s)

Tuner/Reception/Transmission

Frequency band: DECT
Number of channels: 120
Automatic channel selection

Accessories

Batteries
AC/DC adapter
Quick start guide
User manual
Neck cord
Charging base for parent unit: No

Convenience

Battery low indication
Volume control
Auto out of range warning
Sound-level lights
Battery charging indication
Sensitivity control

Technical specifications

Operating temperature range °C: 10 - 40 °C
Storage temperature range: 10-40 °C

Logistic data

F-box dimensions (W x H x D): 220 x 156 x 94 mm

Features

DECT Technology
Energy-saving Smart ECO mode: ECO mode
Sound activation lights: 5 LED lights
Comforting night light
Lullabies
Volume control and sound activation
Indoor range up to: 50 m
Outdoor range up to: 330 metres
Talkback function

Development stages

Stages: Pregnancy, 0–6 months

