

PHILIPS

AVENT

DECT Baby Monitor

Added support

Temperature alert

& 33% more battery power **



SCD565/22



The most reliable connection to your baby Added support for you and your baby

Our new DECT SCD565/22 Baby Monitor delivers complete reassurance. Providing the most reliable connection with crystal clear sound, temperature control, a soothing night light and lullabies for you and your baby.

DECT Technology

- DECT technology guarantees zero interference & 100% privacy
- Dynamic energy saving Smart ECO mode
- Energy saving ECO max
- Reassurance with crystal clear sound
- Choose the best sound level for your surroundings
- 3 LED lights to signal sound
- More flexibility with up to 24 hours of operating time**

Complete reassurance and Complete comfort

- Always know that you are connected
- Range up to 330 meters*
- Rechargeable parent unit
- Comforting night light and lullabies to calm your little one
- Superior operating time
- Stay connected with talk back



asimpleswitch.com

Highlights

3D LED lights



Lights are activated to indicate the level of sound in your baby's room. Even when the Parent Unit is muted.

Crystal clear sound

Hear every tiny giggle, gurgle and hic-up with perfect clarity. DECT technology provides high quality, crystal clear sound so you can hear your baby anytime.

ECO max

Switch on the ECO max to reduce transmission power in the baby room. In the ECO max the units only connect when the baby makes a sound.

Night light and lullabies



There's nothing like a gentle lullaby and a warm tranquil glow of a night light to calm a restless baby. From any room in the house you can select one of 5 relaxing tunes and switch on the night light, helping your baby to drift effortlessly to sleep in no time. (Remote activation not available in US and Canada)

Operating time 24 hours

The small, rechargeable parent unit will give you the freedom of cordless rearing for up to 24 hours before re-charging is required.

Range 330



Indoor range up to 50 meters* Outdoor range up to 330 meters* * The operating range of the baby monitor varies depending on the surroundings and factors that cause interference.

Rechargeable

The rechargeable parent unit enables you to move in and around the home.

Smart ECO mode




The unique Smart ECO mode automatically minimizes your transmission power and increases your battery lifetime. The closer you are to your baby, the less power is needed for a perfect connection (not available in US and Canada).

Talk back



Sometimes all your baby needs is the soothing sound of your voice. With one click of this essential feature you can connect with your baby from anywhere around the home

Temperature sensor



The temperature sensor with customized alert allows you to monitor the climate in baby's room. Your baby can't regulate its body temperature as well as you can and a slight change in temperature can make your baby restless. A customized temperature sensor will immediately alert you, through the digital display on the parent unit, if the climate in your baby's room changes.

Zero interference with DECT



DECT technology guarantees zero interference from any other transmitting product like other baby monitors, cordless phones and cell phones. Data encryption provides a secure and private connection, so you can be sure that you are the only one that can hear your baby.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO₂ emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Features

DECT Technology
Energy saving Smart ECO mode: ECO mode, Yes
Linked and in range indication
Sound activation lights: 3 LED lights
Comforting night light
Talkback function
Soothing lullabies
LCD Screen
Temperature sensor
Indoor range up to: 50m
Outdoor range up to: 330 meters

Power

Operating time on battery: 24 hour(s)
Charging time: 10 hrs
Power Supply: 120 V (US), 220 - 240 V

Tuner/Reception/Transmission

Automatic channel selection
Frequency band: DECT

Convenience

Battery low indication
Battery charging indication
Auto out-of-range warning

Sensitivity control

Volume control
Sound-level lights

Technical specifications

Operating temperature range: 10 - 40 °C
Storage temperature range: 10 - 40 °C

Logistic data

F-box dimensions (W x H x D): 220 x 156 x 94 mm

Development stages

Stage: 0 - 6 months, Pregnancy

