



Philips
TV antenna

UHF
Indoor
20 dB amplified

SDV3220



Receive digital TV signals

with this 20dB amplified antenna

This 20 dB amplified antenna is designed to work with your digital set-top box. Because of the flat panel design, the antenna will pick up the signal you need to watch digital television. Easy to install and easy to power.

Enjoy more programming choices

- 20 db adjustable amplification
- UHF flat panel array for improved reception

Improve your picture quality

- Low noise amplification maintains signal quality
- Illuminated gain control to adjust amplification

Mount it where it looks best and works best

- Various mounting options for best positioning

PHILIPS

TV antenna
UHF Indoor, 20 dB amplified

Specifications

Tuner/Reception/Transmission

- Aerial Output: 75 ohm coaxial (IEC75)
- Tuner bands: UHF
- Antenna cable length: 2m cm
- Gain (antenna + amplifier): 20 dB

Power

- Power Adapter: Included

Accessories

- User Manual: User Manual

Dimensions

- Product weight: .26 kg
- Gross weight: .630 kg
- Tare weight: .260 kg
- Net weight: .370 kg
- Product dimensions (W x H): 75 x 160 mm
- Product thickness: 60 mm

Packaging Data

- Quantity: 1
- EAN/UPC/GTIN: 00 26616 02441 4
- Gross weight: .63 kg
- Tare weight: .260 kg
- Net weight: .370 kg
- Length: 92 mm
- Width: 217 mm
- Height: 280 mm

Outer Carton

- EAN/UPC/GTIN: 87 10895 96530 9
- Quantity: 6
- Gross weight: 4.413 kg
- Tare weight: .693 kg
- Net weight: 3.720 kg
- Length: 558 mm
- Width: 282 mm
- Height: 230 mm

SDV3220/05

Highlights

20 db amplification

20db amplification boosts weak signals, expanding your reception range and allowing you to receive more signals over a greater distance.

UHF flat panel array

The highly efficient UHF flat panel array offers improved reception over conventional loop antennas. Due to the flat design, the antenna concentrates the signal for better reception.

Low noise amplification

Together with the adjustable amplification, low noise amplification ensures you of a great reception range and improves the quality of your signal.

Illuminated gain control

The gain control allows you to adjust your antenna's amplification. The illumination indicates if the power is on and makes the wheel adjustment easy to find.

Various mounting options

Various mounting options allow you to position your antenna where it may best receive broadcast signals. As signals may be either horizontally or vertically polarized, it is important to be able to adjust for both. Includes bracket and 2 meter cable for set top, counter or wall mounting.



Issue date 2014-02-10

Version: 2.0.4

12 NC: 9082 100 07055
EAN: 00 26616 02441 4

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com