


Philips
Bluetooth stereo headset



SHB6000



Tuned for Sports

Secure fit and wireless

Constructed with water proof materials coupled with adjustable earhook that provides secure fit, these wireless headsets have been designed for the fitness enthusiast who wants ultimate freedom while doing sports.

Designed for active use

- Sweat proof
- Washable

Energize You

- Bass thumping stereo sound - fuel for your workout
- Exceptional noise isolation for quality sound at low volume

Innovation for Athletes

- Ultra-soft silicon caps sit comfortably in your ears

One headset for music and calls

- SwitchStream - never miss a beat, never miss a call.
- Integrated mic, volume and track control on headset

Talk freely - handsfree and wireless

- Wireless call management
- Clear calls even in windy or noisy environment

PHILIPS

Highlights

Sweat proof



Designed with a water resistant seal to protect your headphones from sweat related damage

Washable



Constructed with water proof materials allowing you to wash your headphones under running tap water

Bass thumping stereo sound


Acoustics finely tuned to enhance the sporting experience - fuel for your workout

For best sound at low volume

You don't have to turn up the volume in noisy places anymore. Angled Acoustic Pipe and the perfectly sealing earbuds cut off background noise significantly,

delivering the same quality sound at lower volume and a longer battery life.

3-size ultra-soft silicon caps



3 sizes of ultra-soft silicon caps sit comfortably in your ears without adding pressure to them whilst blocking out unwanted noise

SwitchStream

With SwitchStream you will hear a ring tone in your headset when you are receiving a call on your Bluetooth enabled phone. You can then pick up the call from your headset and return to your music after ending the call. Never miss a a beat, never miss a call.

Easy call and music management

Sensitive microphone, volume, call and track controls are all integrated into the headset so you don't need to take out your mobile phones for changing volume, tracks or picking up the call.

Dual mic for noise reduction

This headset is built with dual mic technology for noise reduction. It allows crystal clear call even in windy or noisy environment.

Wireless call management

Manage your call without using your mobile phone. This includes call acceptance, rejection, voice dial and redial. Voice dial and redial have to be supported by your mobile phone.

Specifications

Connectivity

- Bluetooth profiles: A2DP, AVRCP, Handsfree, Headset
- Bluetooth version: 2.1+EDR
- Maximum range: Up to 15 m

Power

- Battery Type: LI-Polymer
- Battery weight: ??
- Music playtime: 4.5 hr
- Rechargeable
- Standby time: 200 hr
- Talk time: 4.5 hr

Sound

- Diaphragm: Mylar Dome
- Frequency response: 15 - 22 000 Hz Hz
- Impedance: 16 Ohm
- Magnet type: Neodymium
- Maximum power input: 20 mW
- Sensitivity: 102 dB
- Speaker diameter: 8.6 mm
- Type: Dynamic
- Voice coil: CCAW

Convenience

- Call Management: Answer/End Call, Reject Call, Last number redial, Voice dial, Microphone mute, Switch between call and music
- Volume control

Accessories

- Charger: USB charging cable
- Pouch: Quick dry pouch
- Quick start guide: Quick start guide

Packaging dimensions

- Packaging dimensions (W x H x D): 13.97 x 19.5 x 8 cm
- EAN: 69 23410 70388 7
- Gross weight: 0.1265 kg
- Nett weight: 0.0715 kg
- Number of products included: 1
- Packaging type: Blister
- Tare weight: 0.055 kg
- Type of shelf placement: Both

Outer Carton

- EAN: 87 12581 55520 7
- Gross weight: 0.5545 kg
- Outer carton (L x W x H): 21.2 x 14.7 x 25 cm
- Nett weight: 0.2145 kg
- Number of consumer packagings: 3
- Tare weight: 0.34 kg



Issue date 2014-09-26

Version: 2.0.6

12 NC: 8670 000 62473
EAN: 69 23410 70388 7

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com