


Philips  
Bluetooth stereo headset



SHB6000



## Sweatproof and washable

Secure fit and wireless

Constructed with water proof materials coupled with adjustable earhook that provides secure fit, these wireless headsets have been designed for the fitness enthusiast who wants ultimate freedom while doing sports.

### Designed for active use

- Sweat proof
- Washable

### Energize you

- Bass thumping stereo sound - fuel for your workout
- Exceptional noise isolation for quality sound at low volume

### Innovation for Athletes

- Ultra-soft silicon caps sit comfortably in your ears

### One headset for music and calls

- SwitchStream - never miss a beat, never miss a call.
- Integrated mic, volume and track control on headset

### Talk freely - handsfree and wireless

- Wireless call management
- Clear calls even in windy or noisy environment

**PHILIPS**

# Highlights

## Sweat proof



Designed with a water resistant seal to protect your headphones from sweat related damage

## Washable



Constructed with water proof materials allowing you to wash your headphones under running tap water

## Bass thumping stereo sound


Acoustics finely tuned to enhance the sporting experience - fuel for your workout

## For best sound at low volume

You don't have to turn up the volume in noisy places anymore. Angled Acoustic Pipe and the perfectly sealing earbuds cut off background noise significantly,

delivering the same quality sound at lower volume and a longer battery life.

## 3-size ultra-soft silicon caps



The 3 sizes of ultra-soft silicon caps of these Philips earphones sit comfortably in your ears without adding pressure to them whilst blocking out unwanted noise.

## SwitchStream

With SwitchStream you will hear a ring tone in your Philips wireless headphones when you are receiving a call on your Bluetooth enabled phone. You can then pick up the call from your headset and return to your music after ending the call. Never miss a beat, never miss a call.

## Easy call and music management

Sensitive microphone, volume, call and track controls are all integrated into the headset so you don't need to take out your mobile phones for changing volume, tracks or picking up the call.

## Dual mic for noise reduction

This headset is built with dual mic technology for noise reduction. It allows crystal clear call even in windy or noisy environment.

## Wireless call management

Manage your call without using your mobile phone. This includes call acceptance, rejection, voice dial and redial. Voice dial and redial have to be supported by your mobile phone.

# Specifications

## Connectivity

- Bluetooth profiles: A2DP, AVRCP, handsfree, headset

## Power

- Battery Type: Li-polymer
- Rechargeable

## Convenience

- Volume control

## Packaging dimensions

- Packaging dimensions (W x H x D): 5.5 x 7.7 x 2.0 inch
- Gross weight: 0.452 lb
- Nett weight: 0.185 lb
- Number of products included: 1
- Packaging type: Blister
- Tare weight: 0.267 lb
- Type of shelf placement: Both
- UPC: 6 09585 19358 1

## Outer Carton

- Gross weight: 1.742 lb
- GTIN: 1 06 09585 19358 8
- Outer carton (L x W x H): 6.6 x 6.2 x 8.0 inch
- Nett weight: 0.556 lb
- Number of consumer packagings: 3
- Tare weight: 1.186 lb



Issue date 2014-02-12

Version: 4.0.10

12 NC: 8670 000 65861  
UPC: 6 09585 19358 1

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)