



Philips  
Bluetooth headphones

**Foldie**  
On-ear  
Black

**SHB8000BK**



## Wireless high precision sound

Excellent isolation and foldable design

The biker-inspired CitiScape Foldie delivers clear, precise sound and excellent noise isolation via a closed acoustic system and premium drivers. With Bluetooth, enjoy music wirelessly and switch between music and calls with ease and style.

### **Total sound immersion on the move**

- 40mm premium neodymium drivers for uncompromised clarity
- Bluetooth 3.0 for unwired music enjoyment and call switching
- Closed acoustic design for greater bass and noise isolation
- Pre-tilted earshells fit any ear for excellent sound sealing

### **Supreme comfort**

- Flexible metal arm designed for long listening comfort
- On-ear soft cushions for added comfort

### **Designed to stun**

- Handcrafted headband inspired by urban bike handle bars
- Compact foldable design for easy portability and storage

### **Design for convenience**

- Bluetooth or corded – enjoy music any way you like!
- Digital noise reduction for clear phone calls

# PHILIPS

Bluetooth headphones  
Foldie On-ear, Black

# Highlights

## 40mm premium neodymium drivers



High performance 40mm neodymium drivers reproduce a wide frequency range accentuated with excellent sound details. Enjoy every nuance in your favorite music – from extended bass notes and warm mid-tones to crystal clear highs.

## Bluetooth 3.0 connection



The CitiScape Foldie features Bluetooth 3.0, which allows you to enjoy your music wirelessly and effortlessly. Its smart controls on the headset is designed to let you easily switch between your music and calls with ease.

## Choice of Bluetooth or corded



Letting you take your pick of not only Bluetooth wireless but also 3.5mm plug-in

musical playback, our new Bluetooth headset really does offer you the best of both worlds! Simply pair up your headset with any Bluetooth-enabled device to enjoy wireless listening pleasure at its crystal-clear best. Alternatively, just plug in the cable to the 3.5mm jack to enjoy the same deeply enriching immersive listening experience. Choice is yours!

## Compact foldable design



Your headphones can be compactly folded for easy storage and portability.

## Digital noise reduction

This noise reduction technology improves the speech intelligibility with ambient noise during voice calls. It will suppress the background noise and echo so that you can enjoy phone calls with improved audio quality in the presence of road noise, babble, wind noise, and etc. The technology estimates and creates an equal but opposite waveform to the noise that reduces the unwanted noise by the process of subtraction.

## Excellent noise isolation



Be part of the city's buzz but not its noise. With the closed acoustic on-ear design, every

SHB8000BK/00

sound detail is isolated, allowing you to enjoy greater music detail as well as extended and dynamic bass.

## Flexible metal arm design



Inspired by bike wiring, the earshells and headband are connected by lightweight but durable metal wiring, ensuring secure long-wearing comfort.

## Handcrafted headband



Inspired by the woven wrapping around bike handle bars, the headband is handcrafted using leatherette for an edgy style statement.

## Precisely tilted earshells

Pre-tilted earshells perfectly fit your ear's natural angle, providing an excellent sound seal so you can truly immerse in your music.

# Specifications

## Sound

- Frequency range: 18 - 20700Hz
- Impedance: 32 ohm
- Magnet type: Neodymium
- Maximum power input: 50 mW
- Speaker diameter: 40 mm
- Acoustic system: Closed

## Design

- Color: Black

## Connectivity

- Audio Connections: 3.5mm Line in
- Bluetooth profiles: A2DP, AVRCP, HFP, HSP
- Maximum range: Up to 15 m

## Accessories

- Quick start guide: Included
- USB cable: Included for charging
- Audio cable: Extra audio cable included

## Product dimensions

- Product dimensions (W x H x D):  
5.7 x 6.5 x 2.7 inch
- Product dimensions (W x H x D):  
14.5 x 16.4 x 6.8 cm
- Weight: 0.128 kg
- Weight: 0.282 lb

## Outer Carton

- Gross weight: 2.564 lb
- Gross weight: 1.163 kg
- GTIN: 1 69 23410 72258 8
- Outer carton (L x W x H): 25.3 x 19.8 x 22.5 cm
- Outer carton (L x W x H): 10.0 x 7.8 x 8.9 inch
- Nett weight: 1.210 lb
- Nett weight: 0.549 kg
- Number of consumer packagings: 3
- Tare weight: 1.354 lb
- Tare weight: 0.614 kg

## Packaging dimensions

- Packaging dimensions (W x H x D):  
19.5 x 20 x 9 cm
- Packaging dimensions (W x H x D):  
7.7 x 7.9 x 3.5 inch
- EAN: 69 23410 72258 1
- Gross weight: 0.313 kg
- Gross weight: 0.690 lb
- Nett weight: 0.183 kg
- Nett weight: 0.403 lb
- Number of products included: 1
- Packaging type: Carton
- Tare weight: 0.13 kg
- Tare weight: 0.287 lb
- Type of shelf placement: Both



Issue date 2016-07-15

Version: 4.1.7

12 NC: 8670 001 05445  
EAN: 69 23410 72258 1

© 2016 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\*\*Functions availability may vary based on mobile phone compatibility.