



Philips  
Bluetooth stereo headset

On-ear  
Red



SHB9100RD

## Pure sound, wired or wireless

With deluxe FloatingCushions

Superior 40mm Neodymium drivers and digital enhancement ensure the SHB9100 headset's unparalleled sound clarity and rich bass. Deluxe, multi-directional FloatingCushions earshells further enhance both wired and wireless listening pleasure.

### Premium sound quality

- Digital enhancement reveals hidden notes and nuances
- 40mm neodymium drivers deliver a lifelike music soundscape
- Advanced echo and noise reduction for crystal clear calls
- MP3 Codec cuts battery consumption without degrading sound

### Longer wearing comfort

- Ultra-comfy, snug-fitting soft memory foam cushions
- FloatingCushions design allows auto-adjustment of earshells

### Fits your life as easily as it fits your ears

- Bluetooth or corded – enjoy music any way you like!
- Handy 0.6m USB cable for easy recharging via your PC
- Bluetooth-enabled wireless music & call control convenience


### Works with all Bluetooth-enabled devices

- Supports Bluetooth 3.0 HSP/HFP/A2DP/AVRCP mobile devices
- Pair two Bluetooth devices simultaneously

# PHILIPS

# Highlights

## Digital enhancement



Booming & superior bass from high performance drivers and digital enhancement.

## 40mm neodymium drivers



Neodymium is a compact but very strong magnetic material. Neodymium produces a strong magnetic field for greater sensitivity in a voice coil, better bass response and a pure balanced sound quality. The 40mm finely tuned neodymium drivers allow you to enjoy clear, detailed yet natural sound for lifelike music experience.

## Echo and noise reduction

Advanced echo and noise reduction for crystal clear calls

## MP3 Codec

MP3 Codec cuts battery consumption without degrading sound

## Memory foam cushions



Your Philips headset integrates comfy, soft leatherette over-ear cushions which hug the contours of your ears so snugly you'll hardly know they were there! Ideal for heads of every size and shape this incredibly effective seal is the ideal way to forget outside distractions and immerse yourself in music for hour after enjoyable hour.

## FloatingCushions design



An innovative deluxe FloatingCushions design with no C-hinges means it's incredibly quick and easy to make full multi-directional, auto-adjustment of the headset to exactly match the contours of your head. The end result is user-friendly ingenuity that ensures optimum stability by evenly distributing itself across your head and ears.

## Choice of Bluetooth or corded


Letting you take your pick of not only Bluetooth wireless but also 3.5mm plug-in

musical playback, our new Bluetooth headset really does offer you the best of both worlds! Simply pair up your headset with any Bluetooth-enabled device to enjoy wireless listening pleasure at its crystal-clear best. Alternatively, just plug in the cable to the 3.5mm jack to enjoy the same deeply enriching immersive listening experience. Choice is yours!

## Handy 0.6m USB charging cable

Handy 0.6m USB cable for easy recharging via your PC

## Wireless music & call control



When it comes to endless music listening pleasure and hassle-free switching between music and calls, simply nothing beats Bluetooth! To enjoy your favorite hits, simply pair up your Philips headset with your Bluetooth-enabled smart phone or tablet. A tap on each earshell's intuitive control is all that's then needed to lower volume or pause a song while you handle incoming and outgoing calls.

## Bluetooth 3.0

Supports Bluetooth 3.0 HSP/HFP/A2DP/AVRCP mobile devices

## Pair two Bluetooth devices

Pair two Bluetooth devices simultaneously

# Specifications

## Connectivity

- Bluetooth profiles: A2DP, AVRCP, HFP, HSP
- Bluetooth version: 2.1+EDR
- Maximum range: Up to 15 m
- Audio Connections: 3.5mm Line in

## Power

- Talk time: 9 hr
- Standby time: 200 hr
- Music play time: 9 hr
- Rechargeable
- Battery Type: LI-Polymer
- Battery weight: 10.6 g

## Sound

- Frequency range: 8 - 23 000Hz
- Magnet type: Neodymium
- Speaker diameter: 40 mm
- Impedance: 32 Ohm
- Maximum power input: 50 mW
- Sensitivity: 108 dB

## Convenience

- Volume control
- Call Management: Answer/End Call, Reject Call, Last number redial, Voice dial, Microphone mute, Switch between call and music

## Accessories

- USB cable: Included for charging
- Audio cable: 1.2 m audio cable for flight mode operation
- Quick start guide: Quick Start Guide

## Packaging dimensions

- EAN: 69 23410 71812 6
- Number of products included: 1
- Packaging type: Carton
- Packaging dimensions (W x H x D): 19.5 x 20 x 8 cm
- Gross weight: 0.356 kg
- Nett weight: 0.213 kg
- Tare weight: 0.143 kg
- Type of shelf placement: Both

## Outer Carton

- GTIN: 1 69 23410 71812 3
- Number of consumer packagings: 3
- Gross weight: 1.379 kg
- Outer carton (L x W x H): 25.5 x 20.8 x 22.4 cm
- Nett weight: 0.639 kg
- Tare weight: 0.74 kg

## Product dimensions

- Product dimensions (W x H x D): 14.9 x 17.8 x 7 cm
- Weight: 0.14 kg



Issue date 2020-07-08

Version: 2.2.5

12 NC: 8670 000 95987  
EAN: 69 23410 71812 6

© 2020 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)