



Philips
Wireless hi-fi headphones

Over-ear
Silver

SHC8535



Wireless freedom, clear sound

With Philips wireless headphones, you can enjoy your music wirelessly at home. It will tune automatically for best reception, provide the best listening experience at home.

You'll forget you're wearing them!

- 3-way adjustment for a better fit and bass performance
- Preformed soft ear-cushions ensure a comfortable fit

The perfect wireless listening experience

- The whole ear is covered to optimize sound quality
- 40mm speaker driver delivers sound without distortion
- Convenient automatic tuning ensures best reception

Always ready to go

- FM Wireless transmission for freedom of movement
- Simple, convenient charging with a wireless dock

PHILIPS

Specifications

Sound

- Acoustic system: closed
- Frequency response: 10 - 22 000 Hz
- Magnet type: Neodymium
- Sensitivity: 100 dB
- Speaker diameter: 40 mm
- Signal/noise ratio: 70 dB

Tuner/Reception/Transmission

- Pilot tone frequency: 19
- Effective range: 100 m
- Carrier frequency range: 863.0 - 865.0 MHz
- Channel separation: >30 dB
- Modulation: FM
- Number of channel: 3

Convenience

- Battery charging indicator
- Automatic power off
- Operating time: +/- 15 hours
- Low battery indicator
- Double PLL

Power

- Power supply headphone: 2 x 1.5 V NiMH R03/AAA
- Power supply transmitter: AC/DC adapter 12V/200mA

Outer Carton

- Gross weight: 3.72 kg
- Outer carton (L x W x H): 39 x 26 x 32.5 cm
- Nett weight: 1.221 kg
- Tare weight: 2.499 kg
- GTIN: 1 69 23410 71053 0
- Number of consumer packagings: 3

Packaging dimensions

- Packaging dimensions (W x H x D): 24 x 32 x 12.2 cm
- Gross weight: 1.032 kg
- Nett weight: 0.407 kg
- Tare weight: 0.625 kg
- EAN: 69 23410 71053 3
- Number of products included: 1
- Packaging type: Carton

Highlights

3-way adjustable ear shells

Enjoy a comfortable fit and experience better bass performance thanks to the three-way adjustable ear shells that fit naturally around your ears.

Full size design

Full-size earshells of these Philips headphones not only cover your whole ear for better sound quality, but also provide space for a larger, higher performance driver.

40 mm speaker driver

The 40 mm speaker driver is made of a composite mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

FM Wireless transmission

With high frequency FM wireless transmission, which can even pass through walls, you can even listen to your music when you're in another room.

Convenient automatic tuning

Convenient automatic tuning ensures best reception

Preformed soft ear-cushions

Preformed soft ear-cushions ensure a comfortable fit

Simple, convenient charging

Simple, convenient charging with a wireless dock

