



Philips  
Headphones with mic

15mm drivers/open-back  
Earbud

SHE2105BK



## Bass sound

### Play music and talk

With 15mm speakers, these earbud headphones are valued for the bass sound. Ergonomics design with slim rubberized caps for long hours of comfort listening. Sensitive microphones and easy control for talking on your mobile phone.

#### **Designed around you**

- Integrated microphone & call button

#### **Music to your ears**

- 15mm speaker driver optimizes wearing comfort
- Bass beat vents allow air movement for better sound

#### **Made to fit you and your lifestyle**

- Slim cap earbud design for best comfort fit

# PHILIPS

Headphones with mic  
15mm drivers/open-back Earbud

SHE2105BK/28

# Specifications

## Packaging dimensions

- Packaging dimensions (W x H x D):  
5 x 17.275 x 2.6 cm
- Packaging dimensions (W x H x D):  
2.0 x 6.8 x 1.0 inch
- Nett weight: 0.0138 kg
- Nett weight: 0.030 lb
- Gross weight: 0.0292 kg
- Gross weight: 0.064 lb
- Tare weight: 0.0154 kg
- Tare weight: 0.034 lb
- UPC: 6 09585 22914 3
- Number of products included: 1
- Packaging type: Blister
- Type of shelf placement: Both

## Outer Carton

- Outer carton (L x W x H): 34.5 x 19.7 x 16.3 cm
- Outer carton (L x W x H): 13.6 x 7.8 x 6.4 inch
- Nett weight: 0.3312 kg
- Nett weight: 0.730 lb
- Gross weight: 1.1496 kg
- Gross weight: 2.534 lb
- Tare weight: 0.8184 kg
- Tare weight: 1.804 lb
- GTIN: 1 06 09585 22914 0
- Number of consumer packagings: 24

## Inner Carton

- Inner carton (L x W x H): 17.9 x 8 x 6 cm

- Inner carton (L x W x H): 7.0 x 3.1 x 2.4 inch
- Nett weight: 0.0414 kg
- Nett weight: 0.091 lb
- Gross weight: 0.1146 kg
- Gross weight: 0.253 lb
- Tare weight: 0.0732 kg
- Tare weight: 0.161 lb
- GTIN: 2 06 09585 22914 7
- Number of consumer packagings: 3

## Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Voice coil: Copper
- Diaphragm: Mylar dome
- Frequency response: 12 - 22 000 Hz
- Impedance: 16 Ohm
- Maximum power input: 50 mW
- Sensitivity: 107 dB
- Speaker diameter: 15 mm
- Type: Dynamic

## Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 1.0 m
- Connector: 3.5 mm stereo
- Type of cable: Copper
- Finishing of connector: Chrome plated
- Microphone: Built-in microphone

# Highlights

## Integrated microphone

With the integrated microphone and call button you can use this Philips headset for music as well as calls from your mobile phone. Enjoy handsfree calling, while easily accepting and ending calls from your headset.

## 15 mm speaker driver

Small enough for optimum wearing comfort and big enough to deliver crisp, non-distorted sound, the 15 mm speaker driver is an ideal size for listening enjoyment.

## Bass Beat vents

Bass beat vents allow air movement for better sound with a deep rich bass.

## Slim cap earbud design

Slim cap is ergonomically designed according to the anatomy of the human ear canal. It fits in the ear securely and comfortably for earbud lovers.



Issue date 2017-05-07

Version: 1.1.5

12 NC: 8670 000 94811  
EAN: 00 60958 52291 43

© 2017 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)