



Extra bass

Soft body for comfy fit

Philips SHE3010 headphones with soft body earbuds offer a soft, comfortable fit. Available in vibrant, eye-catching colors to match your style.

Enjoy quality sound

- 14.8mm speaker drivers for high quality sound
- Neodymium magnets enhance bass performance and sensitivity

Ultimate wearing comfort

- Rubberized front caps for wearing comfort
- Soft body ensures a comfortable fit

Design for convenience

- Flexi-Grip design for durability

Philips
Earbud headphones

14.8mm drivers/open-back
Earbud



SHE3010BL



PHILIPS

Earbud headphones
14.8mm drivers/open-back Earbud

Specifications

Design

- Color: Blue

Sound

- Acoustic system: open
- Magnet type: Neodymium
- Voice coil: copper
- Diaphragm: PET
- Impedance: 16 ohm
- Maximum power input: 25 mW
- Sensitivity: 107 dB
- Speaker diameter: 14.8 mm
- Type: Dynamic
- Frequency response: 9 - 22 000 Hz

Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1 m
- Connector: 3.5 mm
- Finishing of connector: nickel plated
- Type of cable: copper

Packaging dimensions

- EAN: 69 23410 73219 1
- Packaging dimensions (W x H x D):
5.2 x 17.5 x 2.8 cm
- Gross weight: 0.03217 kg

- Nett weight: 0.01167 kg
- Number of products included: 1
- Packaging type: Blister
- Tare weight: 0.0205 kg
- Type of shelf placement: Both

Inner Carton

- Gross weight: 0.12351 kg
- GTIN: 2 69 23410 73219 5
- Inner carton (L x W x H): 17.9 x 8 x 6 cm
- Nett weight: 0.03501 kg
- Number of consumer packagings: 3
- Tare weight: 0.0885 kg

Outer Carton

- Gross weight: 1.21708 kg
- GTIN: 1 69 23410 73219 8
- Outer carton (L x W x H): 34.5 x 19.7 x 16.3 cm
- Nett weight: 0.28008 kg
- Number of consumer packagings: 24
- Tare weight: 0.937 kg

Product dimensions

- Product dimensions (W x H x D):
1.6 x 2.1 x 1.25 cm
- Weight: 0.01167 kg

SHE3010BL/00

Highlights

Flexi-grip

A soft, flexible part protects the cable connection from damage that otherwise would occur due to repeated bending.


Neodymium magnets

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

Soft body


The transparent, rubberized headphone body molds itself to the shape of the ear for comfortable listening.

14.8mm speakers



Large 14.8mm speaker drivers squeezed into earbud headphones deliver high quality sound.

Rubberized front cap



A rubberized front cap provide a totally soft body for wearing comfort.



Issue date 2017-07-12

Version: 3.2.4

12 NC: 8670 001 17078
EAN: 69 23410 73219 1

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com