



Philips  
Headphones with mic

14.8mm drivers/open-back  
Earbud



SHE3015PH



## Extra bass

Soft body for comfy fit

Philips SHE3015 headphones with soft body earbuds offer a comfortable fit. Available in eye-catching colors. The built-in mic and control make handsfree talking on mobile easy.

### Enjoy quality sound

- 14.8mm speaker drivers for high quality sound
- Neodymium magnets enhance bass performance and sensitivity

### Ultimate wearing comfort

- Soft body ensures a comfortable fit
- Rubberized front caps for wearing comfort

### Design for convenience

- Flexi-Grip design for durability
- Built-in microphone switches you from music to phone calls

# PHILIPS

Headphones with mic  
14.8mm drivers/open-back Earbud

# Specifications

## Design

- Color: Pink

## Sound

- Acoustic system: open
- Magnet type: Neodymium
- Voice coil: copper
- Diaphragm: PET
- Impedance: 16 ohm
- Maximum power input: 25 mW
- Sensitivity: 107 dB
- Speaker diameter: 14.8 mm
- Type: Dynamic
- Frequency response: 9 - 22 000 Hz

## Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1 m
- Connector: 3.5 mm
- Finishing of connector: nickel plated
- Type of cable: copper

## Packaging dimensions

- EAN: 69 23410 73228 3
- Packaging dimensions (W x H x D):  
5,2 x 17,5 x 2,8 cm
- Gross weight: 0,0339 kg

- Nett weight: 0,0134 kg
- Number of products included: 1
- Packaging type: Dummy
- Tare weight: 0,0205 kg
- Type of shelf placement: Dummy

## Inner Carton

- Gross weight: 0,1287 kg
- GTIN: 2 69 23410 73228 7
- Inner carton (L x W x H): 17,9 x 8 x 6 cm
- Nett weight: 0,0402 kg
- Number of consumer packagings: 3
- Tare weight: 0,0885 kg

## Outer Carton

- Gross weight: 1,2586 kg
- GTIN: 1 69 23410 73228 0
- Outer carton (L x W x H): 34,5 x 19,7 x 16,3 cm
- Nett weight: 0,3216 kg
- Number of consumer packagings: 24
- Tare weight: 0,9370 kg

## Product dimensions

- Product dimensions (W x H x D):  
1,6 x 2,1 x 1,25 cm
- Weight: 0,0134 kg

SHE3015PH/00

# Highlights

## 14.8mm speakers

Large 14.8mm speaker drivers squeezed into earbud headphones deliver high quality sound.

## Flexi-grip

A soft, flexible part protects the cable connection from damage that otherwise would occur due to repeated bending.

## Neodymium magnets

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

## Rubberized front cap

A rubberized front cap provide a totally soft body for wearing comfort.

## Soft body

The transparent, rubberized headphone body molds itself to the shape of the ear for comfortable listening.

## Built-in microphone

The built-in microphone lets you easily switch from music listening to taking phone calls - easily, so you'll always stay connected with what matter most to you.



Issue date 2016-08-10

Version: 1.2.4

12 NC: 8670 001 17191  
EAN: 06 92341 07322 83

© 2016 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)