




Philips
In-Ear Headset

• Black

SHE3515BK



Clear sound

for your mobile phone

The ultra small in-ear headphones design with soft caps for comfort and compact fit. With small efficient speakers for dynamic bass and clear sound. In-line integrated mic and pick up button for convenient calls.

Enjoy quality sound

- Small efficient speakers reproduce precise sound with bass
- Perfect in-ear seal blocks out external noise

Always ready to go

- A 1.2m long cable that is ideal for outdoor use
- Rubberized cable relief enhances durability

Designed around you

- Integrated microphone & call button

Use them for longer

- 3 interchangeable rubber ear caps for optimal fit in all ear
- Ultra-small for snug comfy in-ear fit

PHILIPS

In-Ear Headset
Black

Highlights

Integrated microphone

With the integrated microphone and call button you can use this Philips headset for music as well as calls from your mobile phone. Enjoy handsfree calling, while easily accepting and ending calls from your headset.

Small efficient speakers



Small efficient speakers for Philips earphones ensure an exact fit and deliver precise sound with powerful bass, ideal for your listening enjoyment.

Perfect in-ear seal

The Super-small speaker drivers of these Philips earphones fit comfortably inside the ear and thanks to the exceptionally snug fit the outside noise is sealed out for high-intensity listening experience.

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

Rubberized cable relief


To extend product life, soft rubber between headphones and cable protects cable connection from damage through repeated bending.

For optimal fit in all ears



With a choice of 3 interchangeable ear caps from size small to large, surely there is a pair that makes these Philips earphones fit your ear perfectly.

Ultra-small in-ear



Ultra small, lightweight in-ear design for best fit in smaller ears, for long hours listening.

SHE3515BK/00

Specifications

Sound

- Magnet type: Neodymium
- Type: Dynamic
- Frequency response: 12 - 23 500 Hz
- Impedance: 16 ohm
- Maximum power input: 50 mW
- Sensitivity: 103 dB
- Speaker diameter: 9 mm
- Acoustic system: Closed
- Diaphragm: Mylar dome

Connectivity

- Cable Connection: Two-parallel, symmetric
- Finishing of connector: Chrome plated
- Microphone: Built-in microphone
- Cable length: 1.2 m
- Connector: 3.5 mm

Packaging dimensions

- Number of products included: 1
- Packaging dimensions (W x H x D): 5 x 17 x 2,5 cm
- Gross weight: 0,0329 kg
- Nett weight: 0,014 kg
- Tare weight: 0,0189 kg
- Packaging dimensions (W x H x D): 2,0 x 6,7 x 1,0 inch
- Gross weight: 0,073 lb
- Nett weight: 0,031 lb
- Tare weight: 0,042 lb
- EAN: 69 23410 71928 4
- Packaging type: Dummy
- Type of shelf placement: Dummy

Outer Carton

- Gross weight: 1,156 kg
- Outer carton (L x W x H): 33,5 x 19 x 14 cm
- Nett weight: 0,336 kg
- Number of consumer packagings: 24
- Tare weight: 0,820 kg
- Gross weight: 2,549 lb
- Outer carton (L x W x H): 13,2 x 7,5 x 5,5 inch
- Nett weight: 0,741 lb
- Tare weight: 1,808 lb
- GTIN: 1 69 23410 71928 1

Inner Carton

- Gross weight: 0,1394 kg
- Inner carton (L x W x H): 18,1 x 7,9 x 6,4 cm
- Nett weight: 0,042 kg
- Number of consumer packagings: 3
- Tare weight: 0,0974 kg
- Gross weight: 0,308 lb
- Inner carton (L x W x H): 7,1 x 3,1 x 2,5 inch
- Nett weight: 0,093 lb
- Tare weight: 0,215 lb
- GTIN: 2 69 23410 71928 8

Product dimensions

- Product dimensions (W x H x D): 0,8 x 0,5 x 0,5 inch
- Product dimensions (W x H x D): 2 x 1,35 x 1,16 cm
- Weight: 0,0134 kg
- Weight: 0,030 lb



Issue date 2013-05-28

Version: 3.0.6

12 NC: 8670 000 98678
EAN: 69 23410 71928 4

© 2013 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com