



Philips  
In-Ear Headset

Pink

SHE3515PK



## Clear sound

for your mobile phone

The ultra small in-ear headphones design with soft caps for comfort and compact fit. With small efficient speakers for dynamic bass and clear sound. In-line integrated mic and pick up button for convenient calls.

### Enjoy quality sound

- Perfect in-ear seal blocks out external noise
- Small efficient speakers reproduce precise sound with bass

### Always ready to go

- A 1.2m long cable that is ideal for outdoor use
- Rubberized cable relief enhances durability

### Designed around you

- Integrated microphone & call button

### Use them for longer

- 3 interchangeable rubber ear caps for optimal fit in all ear
- Ultra-small for snug comfy in-ear fit

# PHILIPS

# Highlights

## Integrated microphone

With the integrated microphone and call button you can use this Philips headset for music as well as calls from your mobile phone. Enjoy handsfree calling, while easily accepting and ending calls from your headset.

## 1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

## Perfect in-ear seal

The Super-small speaker drivers of these Philips earphones fit comfortably inside the ear and thanks to the exceptionally snug fit the outside noise is sealed out for high-intensity listening experience.

## Rubberized cable relief


To extend product life, soft rubber between headphones and cable protects cable connection from damage through repeated bending.

## Small efficient speakers




Small efficient speakers for Philips earphones ensure an exact fit and deliver precise sound with powerful bass, ideal for your listening enjoyment.

## For optimal fit in all ears



With a choice of 3 interchangeable ear caps from size small to large, surely there is a pair that makes these Philips earphones fit your ear perfectly.

## Ultra-small in-ear



Ultra small, lightweight in-ear design for best fit in smaller ears, for long hours listening.

# Specifications

## Sound

- Magnet type: Neodymium
- Type: Dynamic
- Frequency response: 12 - 23 500 Hz
- Impedance: 16 ohm
- Maximum power input: 50 mW
- Sensitivity: 103 dB
- Speaker diameter: 9 mm
- Acoustic system: Closed
- Diaphragm: Mylar dome

## Design

- Color: Pink

## Connectivity

- Cable Connection: Two-parallel, symmetric
- Finishing of connector: Chrome plated
- Microphone: Built-in microphone
- Cable length: 1.2 m
- Connector: 3.5 mm

## Packaging dimensions

- Number of products included: 1
- Packaging dimensions (W x H x D): 5 x 17,3 x 2,7 cm
- Gross weight: 0,0309 kg
- Nett weight: 0,01465 kg
- Tare weight: 0,01625 kg
- Packaging dimensions (W x H x D): 2,0 x 6,8 x 1,1 inch
- Gross weight: 0,068 lb
- Nett weight: 0,032 lb
- Tare weight: 0,036 lb
- EAN: 69 23410 71926 0
- Packaging type: Dummy
- Type of shelf placement: Dummy

## Outer Carton

- Gross weight: 1,2 kg
- Outer carton (L x W x H): 37,4 x 17,4 x 13,6 cm
- Nett weight: 0,35160 kg
- Number of consumer packagings: 24
- Tare weight: 0,84840 kg
- Gross weight: 2,645 lb
- Outer carton (L x W x H): 14,7 x 6,9 x 5,4 inch
- Nett weight: 0,775 lb
- Tare weight: 1,870 lb
- GTIN: 1 69 23410 71926 7

## Inner Carton

- Gross weight: 0,1305 kg
- Inner carton (L x W x H): 18,1 x 8,1 x 6 cm
- Nett weight: 0,04395 kg
- Number of consumer packagings: 3
- Tare weight: 0,08655 kg
- Gross weight: 0,288 lb
- Inner carton (L x W x H): 7,1 x 3,2 x 2,4 inch
- Nett weight: 0,097 lb
- Tare weight: 0,191 lb
- GTIN: 2 69 23410 71926 4

## Product dimensions

- Product dimensions (W x H x D): 0,8 x 0,5 x 0,5 inch
- Product dimensions (W x H x D): 2 x 1,35 x 1,16 cm
- Weight: 0,0109 kg
- Weight: 0,024 lb



Issue date 2016-07-17

Version: 3.0.7

12 NC: 8670 000 98681  
EAN: 69 23410 71926 0

© 2016 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)