




Philips
In-Ear Headset



SHE3595PK

Dynamic bass

Play music and talk

The ultra small in-ear design with soft caps for comfort and compact fit. With small efficient speakers for dynamic bass and clear sound. Sensitive microphones and easy control for talking on your mobile phone.

Designed around you

- Integrated microphone & call button

Enjoy quality sound

- Small efficient speakers reproduce precise sound with bass
- Perfect in-ear seal blocks out external noise

Use them for longer

- 3 interchangeable rubber ear caps for optimal fit in all ear
- Ultra-small for snug comfy in-ear fit

Always ready to go

- A 1.2m long cable that is ideal for outdoor use
- Rubberized cable relief enhances durability



PHILIPS

Highlights

Integrated microphone

With the integrated microphone and call button you can use this Philips headset for music as well as calls from your mobile phone. Enjoy handsfree calling, while easily accepting and ending calls from your headset.

Small efficient speakers




Small efficient speakers for Philips earphones ensure an exact fit and deliver precise sound with powerful bass, ideal for your listening enjoyment.

Perfect in-ear seal


The Super-small speaker drivers of these Philips earphones fit comfortably inside the ear and thanks to the exceptionally snug fit the outside noise is sealed out for high-intensity listening experience.

Ultra-small in-ear



Ultra small, lightweight in-ear design for best fit in smaller ears, for long hours listening.

For optimal fit in all ears



With a choice of 3 interchangeable ear caps from size small to large, surely there is a pair that makes these Philips earphones fit your ear perfectly.

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

Specifications

Sound

- Acoustic system: Closed
- Magnet type: Neodymium
- Voice coil: Copper
- Diaphragm: Mylar dome
- Impedance: 16 Ohm
- Maximum power input: 50 mW
- Sensitivity: 103 dB
- Speaker diameter: 10 mm
- Type: Dynamic
- Frequency response: 12 - 23 500 Hz

Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 1.2 m
- Type of cable: Copper
- Finishing of connector: Chrome plated
- Microphone: Built-in microphone

Packaging dimensions

- Number of products included: 1
- Packaging type: Blister
- UPC: 6 09585 22921 1
- Packaging dimensions (W x H x D): 5 x 17.3 x 2.7 cm
- Packaging dimensions (W x H x D): 2.0 x 6.8 x 1.1 inch
- Gross weight: 0.0293 kg
- Gross weight: 0.065 lb
- Nett weight: 0.013 kg
- Nett weight: 0.029 lb
- Tare weight: 0.036 kg
- Tare weight: 0.0163 lb
- Type of shelf placement: Both

Outer Carton

- Number of consumer packagings: 24
- GTIN: 1 06 09585 22921 8
- Gross weight: 1.19 kg
- Gross weight: 2.623 lb
- Outer carton (L x W x H): 14.7 x 6.9 x 5.4 inch
- Outer carton (L x W x H): 37.4 x 17.4 x 13.6 cm
- Nett weight: 0.312 kg
- Nett weight: 0.688 lb
- Tare weight: 1.936 kg
- Tare weight: 0.878 lb

Inner Carton

- Number of consumer packagings: 3
- GTIN: 2 06 09585 22921 5
- Gross weight: 0.133 kg
- Gross weight: 0.293 lb
- Inner carton (L x W x H): 7.1 x 3.2 x 2.4 inch
- Inner carton (L x W x H): 18.1 x 8.1 x 6 cm
- Nett weight: 0.039 kg
- Nett weight: 0.086 lb
- Tare weight: 0.207 kg
- Tare weight: 0.094 lb



Issue date 2017-05-07

Version: 2.3.8

12 NC: 8670 000 94823
EAN: 00 60958 52292 11

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com