


Philips  
In-Ear Headphones



SHE3682



## Music colors

With transparent housing provide a color mix in-ear headphones. Ergonomics design conforms to ear shape for best fit, small efficient speakers for an precise sound and extra bass performance. Great for long hours of comfortable listening.

### Enjoy quality sound

- Small efficient speakers reproduce precise sound with bass
- Closed type design blocks out ambient noise

### Use them for longer

- Ultra-small for snug comfy in-ear fit
- Comfy, hybrid earcaps for exceptional comfort
- 3 interchangeable rubber ear caps for optimal fit in all ear

### Always ready to go

- A 1.2m long cable that is ideal for outdoor use
- Rubberized cable relief enhances durability
- Cord slider for tidy cable management

# PHILIPS

# Highlights

## 1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

## For optimal fit in all ears



With a choice of 3 interchangeable ear caps from size small to large, surely there is a pair that makes these Philips earphones fit your ear perfectly.

## Comfy, hybrid earcaps

With soft inner and softer outer layers, these earcaps are more comfortable to wear for prolonged listening enjoyment.

## Cord slider

A mini cord slider allows you to adjust the length of the cable and keeps cable tidy when wound up around the device. Also, slide the cord slider towards the earpieces to keep cable always untangle after storage.

## Rubberized cable relief


To extend product life, soft rubber between headphones and cable protects cable connection from damage through repeated bending.

## Small efficient speakers



Small efficient speakers for Philips earphones ensure an exact fit and deliver precise sound with powerful bass, ideal for your listening enjoyment.

## Ultra-small in-ear



Ultra small, lightweight in-ear design for best fit in smaller ears, for long hours listening.

## Closed type design

Sounds around you are perfectly blocked out while the sound from the headphone is kept in a sealed chamber for perfect quality. This makes the headphones great for monitoring during live music or recording sessions.

# Specifications

## Inner Carton

- EAN: 87 12581 53019 8
- Gross weight: 0.3324 kg
- Inner carton (L x W x H): 30.8 x 11.5 x 6.5 cm
- Nett weight: 0.0636 kg
- Number of consumer packagings: 6
- Tare weight: 0.2688 kg

## Outer Carton

- EAN: 87 12581 53022 8
- Gross weight: 1.58 kg
- Outer carton (L x W x H): 31.6 x 24.3 x 14.7 cm
- Nett weight: 0.2544 kg
- Number of consumer packagings: 24
- Tare weight: 1.3256 kg

## Packaging dimensions

- EAN: 87 12581 52378 7
- Number of products included: 1
- Packaging type: Blister
- Packaging dimensions (W x H x D): 5.2 x 17 x 3.5 cm
- Gross weight: 0.042 kg
- Nett weight: 0.0106 kg
- Tare weight: 0.0314 kg

## Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: chrome-plated

## Sound

- Frequency response: 10 - 23 500 Hz
- Impedance: 16 ohm
- Maximum power input: 50 mW
- Sensitivity: 102 dB
- Type: Dynamic



Issue date 2014-02-12

Version: 3.0.12

12 NC: 8670 000 59663  
EAN: 87 12581 52378 7

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)