




Philips BASS+  
Headphones with mic

12.2mm drivers/ closed-back  
In-ear



SHE4305RD

## Feel it. BASS+

Experience suprisingly big sound pumping out of a small, sturdy package. With speaker drivers specially tuned for big bass, Philips BASS+ earphones deliver great sound isolation and wearing stability, so you get the most out of your beats.

### Pure Bass

- Big, bold bass you can feel
- Powerful 12.2 mm speaker drivers
- Great sound isolation

### Comfort fit

- Slim, stable in-ear fit
- Ergonomic design for max comfort

### Convenience

- Remote control for handsfree calls and music

# PHILIPS

Headphones with mic  
12.2mm drivers/ closed-back In-ear


## Highlights

### 12.2 mm drivers




This is big, powerful bass that lets you really feel the beat. Powerful 12.2 mm speaker drivers blast out thumping bass from a sleek, compact package.

### Ergonomic design



Ergonomically designed with oval and angled tubes for a comfortable, natural fit. So you can keep listening for hours in total comfort.

### Handsfree calls



An easy-to-use remote control allows you to play or pause tracks and answer calls with a simple push of a button.

### Slim in-ear fit



With a slim in-ear design that attaches perfectly to your ears, each earphone sits securely for great stability that won't fall out.

### Sound isolation



Designed for optimal passive noise isolation, this in-ear fit ensures you never miss a beat of your music.

### Big, bold bass



This is big, powerful bass that lets you really feel the beat. Don't let the sleek design fool you – specially tuned drivers and bass vents produce ultra-low end frequencies to create a unique BASS+ sound signature.

SHE4305RD/27

## Specifications

### Sound

- Acoustic system: Closed
- Diaphragm: PET
- Magnet type: Neodymium
- Voice coil: CCAW
- Sensitivity: 107 dB
- Speaker diameter: 12.2 mm
- Maximum power input: 30 mW
- Impedance: 32 ohm
- Frequency response: 9 - 23 000 Hz

### Connectivity

- Cable Connection: symmetrical
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: nickel plated

### Packaging dimensions

- Packaging dimensions (W x H x D): 9.5 x 17.5 x 2.5 cm
- Gross weight: 0.044 kg
- Nett weight: 0.013 kg
- Number of products included: 1
- Packaging type: Blister
- Tare weight: 0.031 kg
- Type of shelf placement: Both
- UPC: 8 89446 00847 0

### Inner Carton

- Gross weight: 0.164 kg
- GTIN: 2 08 89446 00847 4
- Inner carton (L x W x H): 18 x 8.2 x 10.5 cm
- Nett weight: 0.039 kg
- Number of consumer packagings: 3
- Tare weight: 0.125 kg

### Outer Carton

- Gross weight: 1.59 kg
- GTIN: 1 08 89446 00847 7
- Outer carton (L x W x H): 38 x 18.1 x 24.8 cm
- Nett weight: 0.312 kg
- Number of consumer packagings: 24
- Tare weight: 1.278 kg

### Product dimensions

- Product dimensions (W x H x D): 3 x 8 x 2.8 cm
- Weight: 0.012 kg

### Design

- Color: Red



Issue date 2017-11-09

Version: 4.2.4

12 NC: 8670 001 45745  
UPC: 8 89446 00847 0

© 2017 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)