



Philips
In-Ear Headphones

Red

SHE7000BR



Compact fit

With micro efficient speakers for strong bass and clear sound. An ultra small in-ear design for compact fit, great for long hours of comfortable listening. Anti-tangle sliders, an ideal cable management to prevent cable tangling.

Enjoy quality sound

- Perfect in-ear seal blocks out external noise
- Small efficient speakers reproduce precise sound with bass

Use them for longer

- 3 interchangeable rubber ear caps for optimal fit in all ear
- Ultra-small for snug comfy in-ear fit

Always ready to go

- A 1.2m long cable that is ideal for outdoor use
- Anti-tangle slider

PHILIPS

Highlights

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

Perfect in-ear seal

The Super-small speaker drivers of these Philips earphones fit comfortably inside the ear and thanks to the exceptionally snug fit the outside noise is sealed out for high-intensity listening experience.

Small efficient speakers




Small efficient speakers for Philips earphones ensure an exact fit and deliver precise sound with powerful bass, ideal for your listening enjoyment.

For optimal fit in all ears



With a choice of 3 interchangeable ear caps from size small to large, surely there is a pair that makes these Philips earphones fit your ear perfectly.

Ultra-small in-ear



Ultra small, lightweight in-ear design for best fit in smaller ears, for long hours listening.

Anti-tangle slider



When storing your headphones there is a risk that the cables tangle if not stored carefully. This makes it a hassle to store the headphones and get them ready for listening. Simply slide the anti-tangle slider towards the earpieces to keep the two earpiece cables neatly together, and to minimize the risk of the cables tangling.

Specifications

Product dimensions

- Product dimensions (W x H x D): 13,9 x 9,12 x 1,1 cm
- Weight: 0,011 kg

Sound

- Acoustic system: Closed
- Frequency response: 10 - 23,500 Hz
- Impedance: 16 Ohms
- Magnet type: Neodymium
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Speaker diameter: 8.6 mm

Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: chrome-plated

Inner Carton

- Number of consumer packagings: 3
- GTIN: 2 69 23410 71059 9
- Gross weight: 0,156 kg
- Inner carton (L x W x H): 18 x 8,5 x 10,5 cm
- Nett weight: 0,033 kg
- Tare weight: 0,123 kg

Outer Carton

- Number of consumer packagings: 24
- GTIN: 1 69 23410 71059 2
- Gross weight: 1,554 kg
- Outer carton (L x W x H): 38,2 x 18,7 x 25 cm
- Nett weight: 0,264 kg
- Tare weight: 1,290 kg

Packaging dimensions

- Type of shelf placement: Dummy
- Packaging dimensions (W x H x D): 9,7 x 17,2 x 2,6 cm
- EAN: 69 23410 71059 5
- Number of products included: 1
- Gross weight: 0,038 kg
- Nett weight: 0,011 kg
- Packaging type: Dummy
- Tare weight: 0,027 kg



Issue date 2015-02-06

Version: 3.0.4

12 NC: 8670 000 79182
EAN: 69 23410 71059 5

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com