

Philips
In-Ear Headphones

• Black

SHE7005



Compact fit

For your mobile phone

SHE7005/00 headphones with micro efficient speakers for strong bass and clear sound. An ultra small in-ear design for compact fit, great for long hours of listening. Anti-tangle sliders, an ideal cable management to prevent cable tangling.

Enjoy quality sound

- Small efficient speakers reproduce precise sound with bass
- Perfect in-ear seal blocks out external noise

Use them for longer

- Ultra-small for snug comfy in-ear fit
- 3 interchangeable rubber ear caps for optimal fit in all ear

Always ready to go

- Anti-tangle slider
- A 1.2m long cable that is ideal for outdoor use

Designed around you

- Extra 3.5mm plug for Nokia, Sony Ericsson, Samsung
- Sensitive and sleek mic for picking up your voice clearly

PHILIPS

Highlights

Small efficient speakers




Small efficient speakers for Philips earphones ensure an exact fit and deliver precise sound with powerful bass, ideal for your listening enjoyment.

Perfect in-ear seal

The Super-small speaker drivers of these Philips earphones fit comfortably inside the ear and thanks to the exceptionally snug fit the outside noise is sealed out for high-intensity listening experience.

Ultra-small in-ear



Ultra small, lightweight in-ear design for best fit in smaller ears, for long hours listening.

For optimal fit in all ears



With a choice of 3 interchangeable ear caps from size small to large, surely there is a pair that makes these Philips earphones fit your ear perfectly.

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

Anti-tangle slider



When storing your headphones there is a risk that the cables tangle if not stored carefully. This makes it a hassle to store the headphones and get them ready for listening. Simply slide the anti-tangle slider towards the earpieces to keep the two earpiece cables neatly together, and to minimize the risk of the cables tangling.

Extra 3.5mm connector

Extra 3.5mm stereo connector for Nokia, Sony Ericsson and Samsung

Sensitive and sleek microphone

Sensitive and sleek microphone for picking up your voice clearly

Specifications

Sound

- Frequency response: 10 Hz - 23,500 Hz
- Impedance: 16 Ohms
- Magnet type: Neodymium
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Speaker diameter: 8.6 mm
- Acoustic system: Closed

Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: chrome-plated

Inner Carton

- Gross weight: 0,377 lb
- Gross weight: 0,171 kg
- GTIN: 2 69 23410 71470 2
- Inner carton (L x W x H): 7,1 x 3,3 x 4,1 inch
- Inner carton (L x W x H): 18 x 8,5 x 10,5 cm
- Nett weight: 0,112 lb
- Nett weight: 0,051 kg
- Number of consumer packagings: 3
- Tare weight: 0,265 lb
- Tare weight: 0,120 kg

Outer Carton

- Gross weight: 3,697 lb
- Gross weight: 1,677 kg
- GTIN: 1 69 23410 71470 5
- Outer carton (L x W x H): 15,0 x 7,4 x 9,8 inch
- Outer carton (L x W x H): 38,2 x 18,7 x 25 cm
- Nett weight: 0,899 lb
- Nett weight: 0,408 kg
- Number of consumer packagings: 24
- Tare weight: 2,798 lb
- Tare weight: 1,269 kg

Packaging dimensions

- Packaging dimensions (W x H x D): 3,8 x 6,8 x 1,0 inch
- Packaging dimensions (W x H x D): 9,7 x 17,2 x 2,6 cm
- EAN: 69 23410 71470 8
- Gross weight: 0,088 lb
- Gross weight: 0,04 kg
- Nett weight: 0,037 lb
- Nett weight: 0,017 kg
- Number of products included: 1
- Packaging type: Dummy
- Tare weight: 0,051 lb
- Tare weight: 0,023 kg
- Type of shelf placement: Dummy

Product dimensions

- Product dimensions (W x H x D): 0,5 x 0,4 x 0,4 inch
- Product dimensions (W x H x D): 1,39 x 0,91 x 1,1 cm
- Weight: 0,017 kg
- Weight: 0,037 lb



Issue date 2013-05-28

Version: 2.1.4

12 NC: 8670 000 90091
EAN: 69 23410 71470 8

© 2013 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com