



Philips
In-Ear Headphones

SHE7750



Turbo Bass

In-ear headphone with turbo-charged bass

High-quality in-ear headphones with turbo-charged bass

Music to your ears

- 24k gold-plated plug ensures an ultra reliable connection
- Copper Cladded Aluminium Wire improves sound quality
- Neodymium magnets enhance bass performance and sensitivity
- Turbo Bass gives you superb deep and dynamic bass tones

Made to fit you and your lifestyle

- 15mm speaker driver optimizes wearing comfort
- Asymmetric cable keeps the cable out the way

Always ready to go

- A 1.2m long cable that is ideal for outdoor use
- Carrying case protects your headphone when not in use
- Durable Flexi-Grip makes a strong flexible connection
- Split cable enables convenient remote control connection

PHILIPS

Specifications

Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 8 - 24 000 Hz
- Impedance: 16 Ohm
- Maximum power input: 50 mW
- Sensitivity: 108 dB
- Speaker diameter: 15 mm
- Type: Dynamic

Connectivity

- Cable Connection: Two-parallel, asymmetric
- Cable length: 0.6 m + 0.6 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold-plated
- Type of cable: OFC

Inner Carton

- Gross weight: .53 kg
- Inner carton (L x W x H): 23.3 x 18.5 x 11.3 cm
- Nett weight: .372 kg
- Tare weight: .158 kg

Outer Carton

- Gross weight: 9.725 kg
- Outer carton (L x W x H): 48.8 x 39.8 x 49.2 cm
- Nett weight: 8.472 kg
- Tare weight: 1.253 kg

Packaging dimensions

- Packaging dimensions (W x H x D): 9.9 x 21.9 x 2.9 cm
- Gross weight: .062 kg
- Nett weight: .018 kg
- Tare weight: .044 kg

Highlights

24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

CCA W voice coil

By using top-quality Copper Cladded Aluminium Wire (CCA W) in the headphone driver's voice coil, the sound quality is considerably improved.

Neodymium magnets

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

Turbo Bass

The unique bass wave design 'turbo-charges' the low tones by directing them towards your ears. The result is a fantastic realistic and a more involved experience.

15 mm speaker driver

Small enough for optimum wearing comfort and big enough to deliver crisp, non-distorted sound, the 15 mm speaker driver is an ideal size for listening enjoyment.

Asymmetric cabling system

This simple yet highly effective solution to cable tangling works effectively by enabling you to hang the cable behind your neck instead of under your chin.

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

Carrying Case

This case is the most convenient way to look after your headphones and prevent cable tangling when not in use.

Flexi-Grip design

A soft, flexible part protects the cable connection from damage that otherwise would occur due to repeated bending.

Split cable

This standard cable has a 3.5mm socket on one end and a 3.5mm plug on the other for extending your freedom of movement with headphones.



Issue date 2014-02-05

Version: 4.1.6

12 NC: 9082 100 06516
EAN: 87 10895 93680 4

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com