




Philips
In-Ear Headphones

SHE7850



Turbo Bass

In-ear headphone with turbo-charged bass

High-quality in-ear headphones with turbo-charged bass, volume control and an unbreakable carrying case for extra protection when not in use.

Music to your ears

- 24 k gold-plated plug ensures an ultra-reliable connection
- Copper Cladded Aluminium Wire improves sound quality
- Neodymium magnet enhances bass performance and sensitivity
- Turbo Bass gives you superb deep and dynamic bass tones

Made to fit you and your lifestyle

- 15 mm speaker driver optimises wearing comfort
- Asymmetric cable keeps the cable out the way

Always ready to go

- A 1.2 m long cable that is ideal for outdoor use
- Carry case protects your headphones when not in use
- Durable Flexi-Grip makes a strong flexible connection
- In-line control that simplifies volume adjustment

PHILIPS

sense and simplicity

Specifications

Sound

- Acoustic system: Open
- Diaphragm: Mylar dome
- Frequency response: 8–24,000 Hz
- Magnet type: Neodymium
- Voice coil: CCAW
- Impedance: 16 Ohm
- Maximum power input: 50 mW
- Sensitivity: 108 dB
- Speaker diameter: 15 mm
- Type: Dynamic

Connectivity

- Cable Connection: Two-parallel, asymmetric
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold-plated
- Type of cable: OFC

Convenience

- Volume control

Accessories

- Carrying case

Inner Carton

- EAN: 87 10895 93684 2
- Number of consumer packages: 6
- Gross weight: 0.839 kg
- Inner carton (L x W x H): 23.3 x 21.8 x 11.3 cm
- Net weight: 0.648 kg
- Tare weight: 0.191 kg

Outer Box

- EAN: 87 10895 93685 9
- Number of consumer packages: 96
- Gross weight: 14.826 kg
- Outer carton (L x W x H): 48.8 x 45.8 x 49.2 cm
- Net weight: 13.424 kg
- Tare weight: 1.402 kg

Packaging dimensions

- EAN: 87 10895 93683 5
- Number of products included: 1
- Packaging type: Blister
- Packaging dimensions (W x H x D): 10 x 22.1 x 3.4 cm
- Gross weight: 0.108 kg
- Net weight: 0.06 kg
- Tare weight: 0.048 kg

Highlights

24 k Gold-plated plug

You can rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

CCAW voice coil

By using top-quality Copper Cladded Aluminium Wire (CCAW) in the headphone driver's voice coil, the sound quality is considerably improved.

Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

Turbo Bass

The unique bass wave design "turbo-charges" the low tones by directing them towards your ears. The result is a fantastically realistic and more involved experience.

15 mm speaker driver

Small enough for optimum wearing comfort and big enough to deliver crisp, non-distorted sound, the 15 mm speaker driver is an ideal size for listening enjoyment.

Asymmetric cabling system

This simple yet highly effective solution to cable tangling works effectively by enabling you to hang the cable behind your neck instead of under your chin.

1.2 metre cable

The ideal cable length to give you the freedom to put your audio device where you want.

Carry case

This case is the most convenient way to look after your headphones and prevent the cable tangling when not in use.

Flexi-Grip design

A soft, flexible part protects the cable connection from damage that otherwise would occur due to repeated bending.

In-line volume control

Adjust the volume to your preferred level without having to go to the audio source unit.



Issue date 2013-01-23

Version: 3.0.7

12 NC: 9082 100 06517
EAN: 87 10895 93683 5

© 2013 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com