



Philips
In-Ear Headphones

White



SHE8000WT



Pump up the bass

Non-slip grip for easy fit

SHE8000WT/10 headphones with tiny, extra-quality speakers that deliver deep bass and crystal clear sound. An integrated cable withstands pulling for durability and comes with a non-slip grip for easy fit. Extra-soft hybrid silicone caps for comfort.

Enjoy quality sound

- Turbo bass air vents for deepest and richest bass
- Exceptional noise isolation for quality sound at low volume

Ultimate wearing comfort

- Ergonomic Angled Acoustic design ensures a natural fit
- Ultra-soft silicone caps sit comfortably in your ears

Always ready to go

- Anti-tangle slider
- A 1.2 m long cable that is ideal for outdoor use
- Durable Flexi-Grip makes a strong flexible connection



asimpleswitch.com



asimpleswitch.com

PHILIPS

Highlights

For deepest and richest bass



Turbo Bass air vents allow air movement for high-fidelity reproduction of the deepest and richest bass.

For best sound at low volume

You don't have to turn up the volume in noisy places any more. Angled Acoustic Pipe and the perfectly sealing ear buds cut off background noise significantly, delivering the same quality sound at a lower volume and with a longer battery life.

1.2 m cable

The ideal cable length to give you the freedom to put your audio device where you want.

Ear fitting design

The design superiority of a slight 15-degree tilt in the Angled Acoustic model based on the anatomy of the human ear achieves a natural fit and supreme comfort.

3-size ultra-soft silicone caps



The 3 sizes of ultra-soft silicone caps of these Philips earphones sit comfortably in your ears without


adding pressure to them whilst blocking out unwanted noise.

Anti-tangle slider



When storing your headphones there is a risk that the cables tangle if not stored carefully. This makes it a hassle to store the headphones and get them ready for listening. Simply slide the anti-tangle slider towards the earpieces to keep the two earpiece cables neatly together and to minimise the risk of the cables tangling.

Flexi-grip design



The soft flexi-grip material that the body of the headphone is sheathed in enhances its performance and extends its durability. It protects the cable connection from damage that otherwise could occur due to repeated bending of the headphone body from frequent contact with the user's fingertips when being put on and removed.

Specifications

Sound

- Acoustic system: Semi-closed
- Diaphragm: Mylar dome
- Frequency response: 8 - -24,000 Hz
- Impedance: 16 Ohm
- Magnet type: Neodymium
- Type: Dynamic
- Voice coil: CCAW
- Sensitivity: 102 dB
- Speaker diameter: 10 mm
- Maximum power input: 30 mW

Connectivity

- Connector: 3.5 mm stereo
- Type of cable: OFC
- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Finishing of connector: Gold-plated



Issue date 2015-07-10

Version: 2.1.9

12 NC: 8670 000 77415
EAN: 69 23410 71042 7

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com