

Philips  
In-Ear Headset



SHE8005



## Pump up the bass

For your mobile phone

With tiny, extra-quality speakers that deliver rich, deep bass, and crystal clear sound. The integrated mic picks up your voice clearly. In-line remote for volume and call control for added convenience.

### Enjoy quality sound

- Angled Acoustic Pipe channels directional and precise sound
- Exceptional noise isolation for quality sound at low volume
- Turbo bass air vents for deepest and richest bass

### Designed around you

- In-line remote for volume and call control
- Sensitive and sleek mic for picking up your voice clearly

### Ultimate wearing comfort

- Ergonomic Angled Acoustic design ensures a natural fit
- Ultra-soft silicon caps sit comfortably in your ears

### Always ready to go

- A 1.2m long cable that is ideal for outdoor use
- Durable Flexi-Grip makes a strong flexible connection
- Anti-tangle slider

# PHILIPS

# Highlights

## For most directional sound

Angled Acoustic Pipe is designed according to the curvature of the human ear canal so that soundwaves from the speaker are directed precisely to your ear drum with the highest definition

## For best sound at low volume

You don't have to turn up the volume in noisy places anymore. Angled Acoustic Pipe and the perfectly sealing earbuds cut off background noise significantly, delivering the same quality sound at lower volume and a longer battery life.

## For deepest and richest bass




Turbo Bass air vents allow air movement for high-fidelity reproduction of the deepest and richest bass.

## 1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

## Flexi-grip design



The soft flexi-grip material that the body of the headphone is sheathed in enhances its performance and extends its durability. It protects the cable connection from damage that otherwise could occur due to repeated bending of the headphone body from frequent contact with the user's fingertips when being put on and removed.

## Ear fitting design

The design superiority of a slight 15-degree tilt in the Angled Acoustic model based on the anatomy of the human ear achieves a natural fit and supreme comfort.

## Anti-tangle slider



When storing your headphones there is a risk that the cables tangle if not stored carefully. This makes it a hassle to store the

headphones and get them ready for listening. Simply slide the anti-tangle slider towards the earpieces to keep the two earpiece cables neatly together, and to minimize the risk of the cables tangling.

## 3-size ultra-soft silicon caps



3 sizes of ultra-soft silicon caps sit comfortably in your ears without adding pressure to them whilst blocking out unwanted noise

## In-line vol and call control



Want to change the volume? Accept or reject a call? The remote features volume and call controls. With this headset control is at your fingertips!

## Sensitive and sleek microphone

Sensitive and sleek microphone for picking up your voice clearly

# Specifications

## Sound

- Acoustic system: Closed
- Diaphragm: Mylar dome
- Frequency response: 10 - 23 500 Hz
- Impedance: 16 Ohm
- Magnet type: Neodymium
- Type: Dynamic
- Voice coil: CCAW
- Sensitivity: 100 dB
- Speaker diameter: 10 mm
- Maximum power input: 15 mW

## Connectivity

- Connector: 3.5 mm stereo
- Microphone: Built-in microphone
- Compatible with:: Blackberry, HTC, iPhone, LG, Motorola, Palm
- Type of cable: OFC
- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Finishing of connector: gold-plated

## Convenience

- Volume control

## Packaging dimensions

- Packaging dimensions (W x H x D): 9.6 x 17.4 x 3.2 cm
- Nett weight: 0.0192 kg
- Gross weight: 0.0622 kg
- Tare weight: 0.043 kg
- EAN: 69 23410 70900 1
- Number of products included: 1
- Packaging type: Blister

## Outer Carton

- Outer carton (L x W x H): 41.8 x 20.5 x 17.9 cm
- Nett weight: 0.4608 kg
- Gross weight: 2.017 kg
- Tare weight: 1.5562 kg
- EAN: 87 12581 59521 0
- Number of consumer packagings: 24

## Inner Carton

- Inner carton (L x W x H): 19.8 x 10.2 x 16.5 cm
- Nett weight: 0.1152 kg
- Gross weight: 0.448 kg
- Tare weight: 0.3328 kg
- EAN: 87 12581 59523 4
- Number of consumer packagings: 6



Issue date 2014-08-06

Version: 4.1.8

12 NC: 8670 000 74631  
EAN: 69 23410 70900 1

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)