



Philips
In ear headphones

Noise isolation



SHE8500



Noise isolation

High quality speakers

In-ear headphones for superb sound. Ultra small quality speakers and choice of 3 cap sizes deliver the sound closer to the ear while also creating a snug fit that block external noise. Choice of cap size also ensures comfort fit.

Music to your ears

- 24k gold-plated plug ensures an ultra reliable connection
- Copper Cladded Aluminium Wire improves sound quality
- Neodymium magnet enhances bass performance and sensitivity
- Passive noise isolation for better sound at lower volume

Made to fit you

- Ergonomically-shaped headphone enhances user comfort
- Asymmetric cable keeps the cable out the way
- 3 interchangeable rubber ear caps for optimal fit in all ear

Always ready to go

- Carrying case protects your headphone when not in use
- Durable Flexi-Grip makes a strong flexible connection
- A 1.2m long cable that is ideal for outdoor use

PHILIPS

sense and simplicity

In ear headphones
Noise isolation

Highlights

24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

Carrying Case

This case is the most convenient way to look after your headphones and prevent cable tangling when not in use.


CCAW voice coil

By using top-quality Copper Cladded Aluminium Wire (CCAW) in the headphone driver's voice coil, the sound quality is considerably improved.

Comfort fit

This headphone is designed around the shape of your ear for extra comfort and more enjoyment during longer periods of listening.

Flexi-grip design



The soft flexi-grip material that the body of the headphone is sheathed in enhances its performance and extends its durability. It protects the cable connection from damage that otherwise could occur due to repeated bending of the headphone body from frequent contact with the user's fingertips when being put on and removed.

Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

Passive noise isolation

The perfect, snug fit inside your ear stops unwanted background noise detracting from the pure pleasure of your favorite music. This means you still enjoy the headphones' superb sound quality at lower volume settings, and also benefit from a longer battery life.

Asymmetric cabling system

This simple yet highly effective solution to cable tangling works effectively by enabling you to hang the cable behind your neck instead of under your chin.

For optimal fit in all ears



With a choice of 3 interchangeable ear caps from size small to large, surely there is a pair that makes these Philips earphones fit your ear perfectly.

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

SHE8500/97

Specifications

Sound

- Voice coil: CCAW
- Type: Dynamic

Connectivity

- Cable Connection: two-parallel, asymmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: OFC

Accessories

- Included: transport case

Packaging dimensions

- Packaging dimensions (W x H x D):
9.9 x 21.9 x 2.9 cm
- Gross weight: .066 kg
- Nett weight: .018 kg
- Tare weight: .048 kg

Outer Carton

- Gross weight: 10.06 kg
- Outer carton (L x W x H): 48.1 x 40 x 48 cm
- Nett weight: 1.728 kg
- Tare weight: 8.332 kg

Inner Carton

- Gross weight: .554 kg
- Inner carton (L x W x H): 23.3 x 18.5 x 11.3 cm
- Nett weight: .396 kg
- Tare weight: .158 kg



Issue date 2013-02-15

Version: 3.0.4

12 NC: 9082 100 05573
EAN: 87 10895 92003 2

© 2013 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com