




Philips
Headphones with mic

10mm drivers/semi-closed back
In-ear



SHE9005

Perfect fit, precise sound

For your mobile phone with volume control

With a vibration-absorbing metal housing, this SHE9005/00 headset with high performance speaker creates bass fidelity, for true-to-life sound. Uniquely curved design enables perfect fit. Comply™ foam tip for perfect noise isolation.

Enjoy quality sound

- Premium metal housing offers accurate sound transmission.
- Perfect in-ear seal blocks exceptional noise
- Exceptional noise isolation for quality sound at low volume

Ultimate wearing comfort

- Uniquely curved design enables easy grip for perfect fit
- Ultra soft memory foam cushions for great comfortable fit
- Ultra-soft silicon caps sit comfortably in your ears

Always ready to go

- Fabric covered cable lasts longer and prevents tangling
- Anti-tangle slider
- Durable Flexi-Grip makes a strong flexible connection

Designed around you

- In-line remote for volume and call control

PHILIPS

Headphones with mic
10mm drivers/semi-closed back In-ear

SHE9005/00

Highlights

Premium metal housing



Housed in superior metal, these earphones are shielded from unnecessary vibration for accurate sound transmission, resulting in smooth bass response and clear mid-to-high range tones.

Precisely tuned acoustics

Perfect in-ear seal of these earphones surprises you with exceptional noise isolation.

For best sound at low volume

You don't have to turn up the volume in noisy places anymore. Angled Acoustic Pipe and the perfectly sealing earbuds cut off background noise significantly, delivering the same quality sound at lower volume and a longer battery life.

Uniquely curved design

A unique curved headphones housing design, enables easy grip and makes it easy to get perfect in ear fit - even on the go.


Soft memory foam cushions



Ultra soft memory foam cushions perfectly shape around the contours for your ears. This

gives you the best fit while you hardly feel them.

3-size ultra-soft silicon caps



The 3 sizes of ultra-soft silicon caps of these Philips earphones sit comfortably in your ears without adding pressure to them whilst blocking out unwanted noise.

Anti-tangle fabric cable


Textile covered cable prevents cable tangling, is very long-lasting and extends the product life.

Anti-tangle slider



When storing your headphones there is a risk that the cables tangle if not stored carefully. This makes it a hassle to store the headphones and get them ready for listening. Simply slide the anti-tangle slider towards the earpieces to keep the two earpiece cables neatly together, and to minimize the risk of the cables tangling.

Flexi-grip design



The soft flexi-grip material that the body of the headphone is sheathed in enhances its performance and extends its durability. It protects the cable connection from damage that otherwise could occur due to repeated bending of the headphone body from frequent contact with the user's fingertips when being put on and removed.

In-line vol and call control



Want to change the volume? Accept or reject a call? The remote features volume and call controls. With this headset control is at your fingertips!

Specifications

Sound

- Acoustic system: Semi-closed
- Diaphragm: Mylar dome
- Frequency response: 7 - 25 000 Hz
- Impedance: 16 Ohm
- Magnet type: Neodymium
- Type: Dynamic
- Voice coil: CCAW
- Sensitivity: 108 dB
- Speaker diameter: 10 mm
- Maximum power input: 30 mW

Connectivity

- Connector: 3.5 mm stereo
- Type of cable: OFC
- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Finishing of connector: gold-plated

Inner Carton

- Inner carton (L x W x H): 18 x 8,6 x 10,5 cm
- Inner carton (L x W x H): 7,1 x 3,4 x 4,1 inch
- Nett weight: 0,0558 kg
- Nett weight: 0,123 lb
- Gross weight: 0,2317 kg
- Gross weight: 0,511 lb
- Tare weight: 0,1759 kg
- Tare weight: 0,388 lb
- GTIN: 2 69 23410 71468 9
- Number of consumer packagings: 3

Outer Carton

- Outer carton (L x W x H): 38 x 19,3 x 25 cm

- Outer carton (L x W x H): 15,0 x 7,6 x 9,8 inch
- Nett weight: 0,4464 kg
- Nett weight: 0,984 lb
- Gross weight: 2,1416 kg
- Gross weight: 4,721 lb
- Tare weight: 1,6952 kg
- Tare weight: 3,737 lb
- GTIN: 1 69 23410 71468 2
- Number of consumer packagings: 24

Packaging dimensions

- Packaging dimensions (W x H x D):
9,5 x 17,5 x 2,7 cm
- Packaging dimensions (W x H x D):
3,7 x 6,9 x 1,1 inch
- Nett weight: 0,0186 kg
- Nett weight: 0,041 lb
- Gross weight: 0,0654 kg
- Gross weight: 0,144 lb
- Tare weight: 0,0468 kg
- Tare weight: 0,103 lb
- EAN: 69 23410 71468 5
- Type of shelf placement: Dummy
- Number of products included: 1
- Packaging type: Dummy

Product dimensions

- Product dimensions (W x H x D): 3 x 6,8 x 2 cm
- Product dimensions (W x H x D):
1,2 x 2,7 x 0,8 inch
- Weight: 0,0186 kg
- Weight: 0,041 lb



Issue date 2015-02-11

Version: 3.1.5

12 NC: 8670 000 90088
EAN: 69 23410 71468 5

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

