



Philips
In-Ear Headset

Black



SHE9005A

Perfect fit, precise sound

Easy grip enables perfect in ear fit

Headphones with vibration-absorbing metal housing. High performance speaker create bass fidelity, for true-to-life sound. Uniquely curved design for perfect fit. Comply™ foam tip for perfect noise isolation. Fabric cable prevents tangle.

Enjoy quality sound

- Exceptional noise isolation for quality sound at low volume
- Premium metal housing offers accurate sound transmission.
- Perfect in-ear seal blocks exceptional noise

Designed around you

- Integrated microphone & call button
- Personalize your sound and button via Philips Headset App

Ultimate wearing comfort

- Ultra-soft silicon caps sit comfortably in your ears
- Ultra soft memory foam cushions for great comfortable fit
- Uniquely curved design enables easy grip for perfect fit


Always ready to go

- Anti-tangle slider
- Durable Flexi-Grip makes a strong flexible connection

PHILIPS

Highlights

3-size ultra-soft silicon caps



The 3 sizes of ultra-soft silicon caps of these Philips earphones sit comfortably in your ears without adding pressure to them whilst blocking out unwanted noise.

For best sound at low volume

You don't have to turn up the volume in noisy places anymore. Angled Acoustic Pipe and the perfectly sealing earbuds cut off background noise significantly, delivering the same quality sound at lower volume and a longer battery life.

Soft memory foam cushions



Ultra soft memory foam cushions perfectly shape around the contours for your ears. This gives you the best fit while you hardly feel them.

Precisely tuned acoustics

Perfect in-ear seal of these earphones surprises you with exceptional noise isolation.

Premium metal housing




Housed in superior metal, these earphones are shielded from unnecessary vibration for accurate sound transmission, resulting in smooth bass response and clear mid-to-high range tones.

Uniquely curved design

A unique curved headphones housing design, enables easy grip and makes it easy to get perfect in ear fit - even on the go.

Integrated microphone




With the integrated microphone and call button you can use this Philips headset for

music as well as calls from your mobile phone. Enjoy handsfree calling, while easily accepting and ending calls from your headset.

Your own personalization

Download the Philips Headset App to personalize the sound of your headset as well as the remote to Answer/ End call, Play/ Pause music, Adjust volume +/-, and Change tracks.

Flexi-grip design



The soft flexi-grip material that the body of the headphone is sheathed in enhances its performance and extends its durability. It protects the cable connection from damage that otherwise could occur due to repeated bending of the headphone body from frequent contact with the user's fingertips when being put on and removed.

Specifications

Sound

- Acoustic system: Closed
- Diaphragm: Mylar dome
- Frequency response: 17 - 23000 Hz
- Impedance: 16 Ohm
- Magnet type: Neodymium
- Type: Dynamic
- Voice coil: CCAW
- Sensitivity: 108 dB
- Speaker diameter: 10 mm
- Maximum power input: 30 mW

Connectivity

- Connector: 3.5 mm stereo
- Type of cable: OFC
- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Finishing of connector: gold-plated

Packaging dimensions

- Packaging dimensions (W x H x D):
9,5 x 17,5 x 4 cm
- Packaging dimensions (W x H x D):
3,7 x 6,9 x 1,6 inch
- Nett weight: 0,0195 kg
- Nett weight: 0,043 lb
- Gross weight: 0,0605 kg
- Gross weight: 0,133 lb
- Tare weight: 0,0410 kg
- Tare weight: 0,090 lb
- EAN: 69 23410 71525 5
- Number of products included: 1
- Packaging type: Dummy
- Type of shelf placement: Dummy

Outer Carton

- Outer carton (L x W x H): 38 x 29,5 x 25,5 cm
- Outer carton (L x W x H): 15,0 x 11,6 x 10,0 inch
- Nett weight: 0,4680 kg
- Nett weight: 1,032 lb
- Gross weight: 2,425 kg
- Gross weight: 5,346 lb
- Tare weight: 1,9570 kg
- Tare weight: 4,314 lb
- GTIN: 1 69 23410 71525 2
- Number of consumer packagings: 24

Inner Carton

- Inner carton (L x W x H): 18 x 13,5 x 10,8 cm
- Inner carton (L x W x H): 7,1 x 5,3 x 4,3 inch
- Nett weight: 0,0585 kg
- Nett weight: 0,129 lb
- Gross weight: 0,247 kg
- Gross weight: 0,545 lb
- Tare weight: 0,1885 kg
- Tare weight: 0,416 lb
- GTIN: 2 69 23410 71525 9
- Number of consumer packagings: 3

Product dimensions

- Product dimensions (W x H x D):
1,0 x 4,7 x 0,5 inch
- Product dimensions (W x H x D):
2,5 x 12 x 1,15 cm
- Weight: 0,015 kg
- Weight: 0,033 lb



Issue date 2015-01-17

Version: 3.5.7

12 NC: 8670 000 89552
EAN: 69 23410 71525 5

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

