



Philips  
In-Ear Headset

## Perfect fit, precise sound

Easy grip enables perfect in ear fit

With a vibration-absorbing metal housing, these high performance speaker create bass fidelity, for true-to-life sound. Uniquely curved design enables perfect fit. Comply™ foam tip for perfect noise isolation. Fabric cable prevents tangle.



SHE9005A

### Enjoy quality sound

- Exceptional noise isolation for quality sound at low volume
- Premium metal housing offers accurate sound transmission.
- Perfect in-ear seal blocks exceptional noise

### Designed around you

- Integrated microphone & call button
- Personalize your sound and button via Philips Headset App

### Ultimate wearing comfort

- Ultra-soft silicon caps sit comfortably in your ears
- Ultra soft memory foam cushions for great comfortable fit
- Uniquely curved design enables easy grip for perfect fit


### Always ready to go

- Durable Flexi-Grip makes a strong flexible connection
- Anti-tangle slider
- Fabric covered cable lasts longer and prevents tangling

# PHILIPS

# Highlights

## 3-size ultra-soft silicon caps



The 3 sizes of ultra-soft silicon caps of these Philips earphones sit comfortably in your ears without adding pressure to them whilst blocking out unwanted noise.

## Anti-tangle fabric cable

Textile covered cable prevents cable tangling, is very long-lasting and extends the product life.

## Anti-tangle slider




When storing your headphones there is a risk that the cables tangle if not stored carefully. This makes it a hassle to store the headphones and get them ready for listening. Simply slide the anti-tangle slider towards the earpieces to keep the two earpiece cables neatly together, and to minimize the risk of the cables tangling.

## For best sound at low volume

You don't have to turn up the volume in noisy places anymore. Angled Acoustic Pipe and the

perfectly sealing earbuds cut off background noise significantly, delivering the same quality sound at lower volume and a longer battery life.

## Flexi-grip design



The soft flexi-grip material that the body of the headphone is sheathed in enhances its performance and extends its durability. It protects the cable connection from damage that otherwise could occur due to repeated bending of the headphone body from frequent contact with the user's fingertips when being put on and removed.

## Soft memory foam cushions



Ultra soft memory foam cushions perfectly shape around the contours for your ears. This gives you the best fit while you hardly feel them.

## Precisely tuned acoustics

Perfect in-ear seal of these earphones surprises you with exceptional noise isolation.

## Premium metal housing




Housed in superior metal, these earphones are shielded from unnecessary vibration for accurate sound transmission, resulting in smooth bass response and clear mid-to-high range tones.

## Uniquely curved design

A unique curved headphones housing design, enables easy grip and makes it easy to get perfect in ear fit - even on the go.

## Integrated microphone



With the integrated microphone and call button you can use this Philips headset for music as well as calls from your mobile phone. Enjoy handsfree calling, while easily accepting and ending calls from your headset.

## Your own personalization

Download the Philips Headset App to personalize the sound of your headset as well as the remote to Answer/ End call, Play/ Pause music, Adjust volume +/-, and Change tracks.

# Specifications

## Product dimensions

- Product dimensions (W x H x D):  
2,5 x 1,2 x 1,15 cm
- Product dimensions (W x H x D):  
1,0 x 0,5 x 0,5 inch
- Weight: 0,015 kg
- Weight: 0,033 lb

## Sound

- Acoustic system: Closed
- Diaphragm: Mylar dome
- Frequency response: 17 - 23000 Hz
- Impedance: 16 Ohm
- Magnet type: Neodymium
- Type: Dynamic
- Voice coil: CCAW
- Sensitivity: 108 dB
- Speaker diameter: 10 mm
- Maximum power input: 30 mW

## Connectivity

- Connector: 3.5 mm stereo
- Type of cable: OFC
- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Finishing of connector: gold-plated

## Packaging dimensions

- Type of shelf placement: Dummy
- Packaging dimensions (W x H x D):  
9,5 x 17,5 x 4 cm
- Packaging dimensions (W x H x D):  
3,7 x 6,9 x 1,6 inch

- Nett weight: 0,015 kg
- Nett weight: 0,033 lb
- Gross weight: 0,061 kg
- Gross weight: 0,134 lb
- Tare weight: 0,046 kg
- Tare weight: 0,101 lb
- EAN: 69 23410 71525 5
- Number of products included: 1
- Packaging type: Dummy

## Outer Carton

- Outer carton (L x W x H): 39 x 29,5 x 25,5 cm
- Outer carton (L x W x H): 15,4 x 11,6 x 10,0 inch
- Nett weight: 0,360 kg
- Nett weight: 0,794 lb
- Gross weight: 2,425 kg
- Gross weight: 5,346 lb
- Tare weight: 2,065 kg
- Tare weight: 4,552 lb
- GTIN: 1 69 23410 71525 2
- Number of consumer packagings: 24

## Inner Carton

- Inner carton (L x W x H): 18 x 13,5 x 10,8 cm
- Inner carton (L x W x H): 7,1 x 5,3 x 4,3 inch
- Nett weight: 0,045 kg
- Nett weight: 0,099 lb
- Gross weight: 0,247 kg
- Gross weight: 0,544 lb
- Tare weight: 0,202 kg
- Tare weight: 0,445 lb
- GTIN: 2 69 23410 71525 9
- Number of consumer packagings: 3



Issue date 2013-09-18

Version: 2.5.6

12 NC: 8670 000 89552  
EAN: 69 23410 71525 5

© 2013 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

