



Ultra sound

3 cap sizes for optimal fit

Revel in the ultra sound performance of the Philips SHE9503/10 earphones. With its exceptionally snug fit and powerful Neodymium speaker drivers you can enjoy the most outstanding sound performance an in-ear headphone can deliver.

Music to your ears

- Passive noise isolation for better sound at lower volume
- Neodymium magnets enhance bass performance and sensitivity
- Copper Cladded Aluminium Wire improves sound quality
- 24k gold-plated plug ensures an ultra reliable connection

Made to fit you and your lifestyle

- 3 interchangeable rubber ear caps for optimal fit in all ear
- Ergonomically-shaped headphone enhances user comfort
- Asymmetric cable keeps the cable out the way
- Super soft rubber caps for sensational comfort

Always ready to go

- Carrying case protects your headphone when not in use
- A 1.2m long cable that is ideal for outdoor use
- Durable Flexi-Grip makes a strong flexible connection
- Split cable enables convenient remote control connection

Philips
In-Ear Headphones

Black

SHE9503



PHILIPS

Specifications

Product dimensions

- Product dimensions (W x H x D):
1,3 x 3,33 x 2,12 cm
- Weight: 0,02 kg

Sound

- Acoustic system: open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 17 - 23 000 Hz
- Impedance: 16 ohm
- Maximum power input: 30 mW
- Sensitivity: 102 dB
- Speaker diameter: 10 mm
- Type: Dynamic

Connectivity

- Cable Connection: two-parallel, asymmetric
- Cable length: 0.6 m + 0.6 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: OFC

Accessories

- Included: transport case
- Extension cable: 1.2 m

Inner Carton

- Gross weight: 0,243 kg
- Inner carton (L x W x H): 18,5 x 10,5 x 10,4 cm
- Nett weight: 0,06 kg
- Tare weight: 0,183 kg
- EAN: 87 12581 49803 0
- Number of consumer packagings: 3

Outer Carton

- Gross weight: 2,286 kg
- Outer carton (L x W x H): 38,7 x 22,7 x 23,5 cm
- Nett weight: 0,48 kg
- Tare weight: 1,806 kg
- EAN: 87 12581 49804 7
- Number of consumer packagings: 24

Packaging dimensions

- Type of shelf placement: Dummy
- Packaging dimensions (W x H x D):
9,5 x 17,5 x 3 cm
- Gross weight: 0,063 kg
- Nett weight: 0,02 kg
- Tare weight: 0,043 kg
- EAN: 87 12581 49802 3
- Number of products included: 1
- Packaging type: Dummy

Highlights

Passive noise isolation

The perfect, snug fit inside your ear stops unwanted background noise detracting from the pure pleasure of your favorite music. This means you still enjoy the headphones' superb sound quality at lower volume settings, and also benefit from a longer battery life.

Neodymium magnets

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

CCA W voice coil

By using top-quality Copper Cladded Aluminium Wire (CCA W) in the headphone driver's voice coil, the sound quality is considerably improved.

24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

For optimal fit in all ears

With a choice of 3 interchangeable ear caps from size small to large, surely there is a pair that makes these Philips earphones fit your ear perfectly.

Comfort fit

This headphone is designed around the shape of your ear for extra comfort and more enjoyment during longer periods of listening.

Asymmetric cabling system

This simple yet highly effective solution to cable tangling works effectively by enabling you to hang the cable behind your neck instead of under your chin.

Super soft rubber caps

The ultra soft rubber material on the rubber caps are sensational to the touch and adapts effortlessly to your ear. In-ear headphones have never been this comfortable.

Carrying Case

This case is the most convenient way to look after your headphones and prevent cable tangling when not in use.

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

Flexi-Grip design

A soft, flexible part protects the cable connection from damage that otherwise would occur due to repeated bending.

Split cable

This standard cable has a 3.5mm socket on one end and a 3.5mm plug on the other for extending your freedom of movement with headphones.

