



Philips
Portable Gaming
Headphone

SHG2100



Lightweight and ultra compact

Extra comfort

Mini headband style headphones that folds neatly into pocket-sized compact. Special forward facing speaker provide extra comfort and fit all ears.

Always ready to go

- A 1.2m long cable that is ideal for outdoor use
- Foldable for compactness, fit easily in your pocket

Made to fit you and your lifestyle

- 15mm speaker driver optimizes wearing comfort
- Ultra lightweight headband improves comfort and fit

Music to your ears

- 24k gold-plated plug ensures an ultra reliable connection
- Copper Cladded Aluminium Wire improves sound quality
- Forward facing style to fit all ears for better comfort.
- Neodymium magnets enhance bass performance and sensitivity

PHILIPS

Specifications

Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 10 - 20 000 Hz
- Impedance: 16 Ohm
- Maximum power input: 50 mW
- Sensitivity: 102 dB
- Speaker diameter: 15 mm
- Type: Dynamic

Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold-plated
- Type of cable: OFC

Inner Carton

- Gross weight: .851 kg
- Inner carton (L x W x H): 26.3 x 25.2 x 20.9 cm
- Nett weight: .561 kg
- Tare weight: .29 kg

Outer Carton

- Gross weight: 8.608 kg
- Outer carton (L x W x H): 55.3 x 53.1 x 45.5 cm
- Nett weight: 6.808 kg
- Tare weight: 1.8 kg

Packaging dimensions

- Packaging dimensions (W x H x D):
17.5 x 22 x 3.6 cm
- Gross weight: .094 kg
- Nett weight: .028 kg
- Tare weight: .066 kg

Highlights

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

15 mm speaker driver

Small enough for optimum wearing comfort and big enough to deliver crisp, non-distorted sound, the 15 mm speaker driver is an ideal size for listening enjoyment.

24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

CCA W voice coil

By using top-quality Copper Cladded Aluminium Wire (CCA W) in the headphone driver's voice coil, the sound quality is considerably improved.

Forward facing style

Designed to be forward facing style, to release most of the clamping force on the ears, for better comfort.

Neodymium magnets

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

Ultra lightweight headband

The slim, lightweight stainless steel headband is so light you'll hardly notice you're wearing it.

Foldable for compactness

The headphone is designed to fold extremely small, so it fits in your pocket.



Issue date 2014-02-05

Version: 4.0.6

12 NC: 9082 100 09344
EAN: 87 10895 98810 0

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com