



PC Gaming

Extra Bass

This dedicated gaming headset delivers extra bass while its soft cushions provide enhanced wearing comfort for longer gaming sessions. The detachable microphone tube enhances the high sensitivity microphone performance for clear commands.

Extra Bass

- 40mm drivers for extra bass

Gaming comfort

- Soft cushions for long gaming comfort

Voice clarity

- Hi sensitivity mini microphone for everyday chat
- Detachable microphone tube for clear voice commands

Always in control

- Inline mute & volume controls for quick adjustments

Philips
PC Gaming Headset

Detachable microphone
Black



SHG7210



PHILIPS

Specifications

Design

- Wearing style: Headband

Sound

- Acoustic system: Closed
- Magnet type: Neodymium
- Type: Dynamic
- Maximum power input: 100 mW
- Speaker diameter: 40 mm
- Headphones frequency response: 20 - 20,000 Hz
- Headphones impedance: 32 Ohm
- Headphones sensitivity: 98 dB
- Microphone frequency response: 100 - 4,000 Hz
- Microphone impedance: 2.2k Ohm
- Microphone sensitivity: -42 dB
- Microphone cartridge: 4 mm

Connectivity

- Cable length: 2 m
- Connector: 2 x 3.5 mm
- Type of cable: Copper

Convenience

- Volume control
- Mute switch

Product dimensions

- Product dimensions (W x H x D):

- 15,6 x 18 x 6,6 cm
- Weight: 0,111 kg

Packaging dimensions

- Packaging dimensions (W x H x D): 19,5 x 22,2 x 7,5 cm
- Gross weight: 0,231 kg
- Nett weight: 0,111 kg
- Tare weight: 0,12 kg
- EAN: 69 23410 71265 0
- Number of products included: 1
- Packaging type: Dummy
- Type of shelf placement: Dummy

Inner Carton

- Gross weight: 1,621 kg
- GTIN: 2 69 23410 71265 4
- Inner carton (L x W x H): 47,5 x 21,5 x 20,7 cm
- Nett weight: 0,666 kg
- Number of consumer packagings: 6
- Tare weight: 0,955 kg


Outer Carton

- Gross weight: 7,432 kg
- GTIN: 1 69 23410 71265 7
- Outer carton (L x W x H): 49,5 x 45,5 x 45,5 cm
- Nett weight: 2,664 kg
- Number of consumer packagings: 24
- Tare weight: 4,768 kg

SHG7210/97


Highlights

40mm Neodymium driver




40mm Neodymium driver deliver extra Bass for an immersive gaming experience.

Extra soft cushions




Extra soft cushions provide enhanced wearing comfort for even longer gaming sessions.

Hi sensitivity mini microphone



The detachable microphone tube enhances the high sensitivity microphone performance for clear commands.

Inline mute and volume control



Convenient inline mute and volume controls allow for quick adjustments.



Issue date 2015-01-15

Version: 3.13.8

12 NC: 8670 000 84113
EAN: 69 23410 71265 0

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com