



Philips
In-Ear Headphones

SHH2610



Mix & Match

Match your Nokia XpressMusic phone

These in-ear headphones come with interchangeable earpiece caps to match your style and your Nokia XpressMusic phone. Bass vents optimise the acoustic airflow for a strong sound performance.

Music to your ears

- Neodymium magnet enhances bass performance and sensitivity
- Twin vents balance the high sounds and bass tones

Made to fit you and your lifestyle

- 15 mm speaker driver optimises wearing comfort
- Ear cushions improve wearing comfort and bass response
- Choose the interchangeable cap that matches your style

Always ready to go

- Durable Flexi-Grip makes a strong flexible connection
- Split cable enables convenient remote control connection

Fits your music phone

- Microphone-friendly cable length
- Made for Nokia XpressMusic

PHILIPS
sense and simplicity

Specifications

Sound

- **Acoustic system:** Open
- **Magnet type:** Neodymium
- **Voice coil:** Copper
- **Diaphragm:** Mylar dome
- **Frequency response:** 12 - 22,000 Hz
- **Impedance:** 16 Ohm
- **Maximum power input:** 50 mW
- **Sensitivity:** 100 dB
- **Speaker diameter:** 15 mm
- **Type:** Dynamic

Connectivity

- **Cable Connection:** Two-parallel, symmetric
- **Cable length:** 0.35 m + 1 m
- **Connector:** 3.5 mm stereo
- **Finishing of connector:** Chrome-plated
- **Type of cable:** Copper

Accessories

- Extension cable

Inner Box

- **Inner carton (L x W x H):** 18.4 x 18 x 11.8 cm
- **Gross weight:** 0.491 kg
- **Net weight:** 0.162 kg
- **Tare weight:** 0.329 kg

Outer Box

- **Outer carton (L x W x H):** 39 x 38.2 x 51.2 cm
- **Gross weight:** 9.156 kg
- **Net weight:** 2.592 kg
- **Tare weight:** 6.564 kg

Packaging dimensions

- **Packaging dimensions (W x H x D):** 10 x 17.6 x 2.7 cm
- **Gross weight:** 0.059 kg
- **Net weight:** 0.027 kg
- **Tare weight:** 0.032 kg

Product highlights

Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

Twin vents

Specially designed vents that channel the air balance the high tones and bass for a more rounded listening experience.

15 mm speaker driver

Small enough for optimum wearing comfort and big enough to deliver crisp, non-distorted sound, the 15 mm speaker driver is an ideal size for listening enjoyment.

Comfortable ear cushions

The special shape and luxurious materials used for the ear cushions ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

Interchangeable caps

Choose one of the three interchangeable earpiece cap sets, each with different styling and colours, to suit your taste and mood.

Flexi-Grip design

A soft, flexible part protects the cable connection from damage that otherwise would occur due to repeated bending.

Microphone-friendly headphone

The cable length of this headphone is designed to optimise sound picked up from the microphone of your hands-free connector. It also optimises overall cable length to the mobile phone.

Split cable

This standard cable has a 3.5 mm socket on one end and a 3.5 mm plug on the other for extending your freedom of movement with headphones.

Made for Nokia XpressMusic

This product has been designed for use with Nokia XpressMusic phones. Extensive testing has been carried out with these phones to make sure you will get the best out of your phone in combination with this Philips product.



Issue date 2008-12-17

Version: 2.1.5

12 NC: 8670 000 34287
EAN: 87 12581 36682 7

© 2008 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com