


Philips  
In-Ear Headset



SHH3580



## Small yet loud

for your mobile phones

The ultra small in-ear design conforms to ear shape for best fit. Quality speakers provides powerful sound. The integrated mic picks up your voice clearly. It is ideal for long hours of music listening and conversation.

### Enjoy quality sound

- Angled Acoustic Pipe channels directional and precise sound
- Perfect in-ear seal blocks out external noise
- Small efficient speakers reproduce precise sound with bass

### Supreme comfort

- 3 interchangeable rubber ear caps for optimal fit in all ear
- Ultra-small for snug comfy in-ear fit

### Designed around you

- Integrated microphone & call button
- 3.5mm plug for Blackberry, HTC, iPhone, LG, Motorola, Palm
- Extra 3.5mm plug for Nokia, Sony Ericsson, Samsung

### Use them for longer

- A 1.2m long cable that is ideal for outdoor use
- Rubberized cable relief enhances durability

# PHILIPS

# Specifications

## Inner Carton

- EAN: 87 12581 55526 9
- Gross weight: 0.1752 kg
- Inner carton (L x W x H): 10.6 x 8.2 x 19.1 cm
- Nett weight: 0.04956 kg
- Number of consumer packagings: 3
- Tare weight: 0.12564 kg

## Outer Carton

- EAN: 87 12581 55525 2
- Gross weight: 1.65 kg
- Outer carton (L x W x H): 34.8 x 22.6 x 20.9 cm
- Nett weight: 0.39648 kg
- Number of consumer packagings: 24
- Tare weight: 1.25352 kg

## Packaging dimensions

- Number of products included: 1
- Packaging type: Blister
- Packaging dimensions (W x H x D): 9.5 x 17 x 2.5 cm
- EAN: 69 23410 70393 1
- Gross weight: 0.04202 kg

- Nett weight: 0.01652 kg
- Tare weight: 0.0255 kg

## Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 1.2m
- Connector: 3.5mm stereo
- Finishing of connector: Chrome plated
- Microphone: Built-in microphone
- Type of cable: Copper

## Sound

- Acoustic system: Semi-open
- Diaphragm: Mylar dome
- Frequency response: 12-23 500 Hz
- Impedance: 16 Ohm
- Magnet type: Neodymium
- Maximum power input: 50 mW
- Sensitivity: 102 dB
- Speaker diameter: 8 mm
- Type: Dynamic
- Voice coil: CCAW

# Highlights

## For most directional sound

Angled Acoustic Pipe is designed according to the curvature of the human ear canal so that soundwaves from the speaker are directed precisely to your ear drum with the highest definition

## Perfect in-ear seal

The Super-small speaker drivers fit comfortably inside the ear and thanks to the exceptionally snug fit the outside noise is sealed out for high-intensity listening experience.


## Integrated microphone

With the integrated microphone and call button you can use this headset for music as well as calls from your mobile phone. Enjoy handsfree calling, while easily accepting and ending calls from your headset.

## For optimal fit in all ears

With a choice of 3 interchangeable ear caps from size small to large, surely there is a pair that fits your ear perfectly.

## Ultra-small in-ear



Ultra small, lightweight in-ear design for best fit in smaller ears, for long hours listening.

## Small efficient speakers

Small efficient speakers for in-ear headphones ensure an exact fit and deliver precise sound with powerful bass, ideal for your listening enjoyment.

## 3.5mm stereo connector

3.5mm stereo connector for Blackberry, HTC, iPhone, LG, Motorola and Palm

## Extra 3.5mm connector

Extra 3.5mm stereo connector for Nokia, Sony Ericsson and Samsung

## 1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

## Rubberized cable relief

To extend product life, soft rubber between headphones and cable protects cable connection from damage through repeated bending.



Issue date 2013-09-18

Version: 1.0.9

12 NC: 8670 000 65863  
EAN: 69 23410 70393 1

© 2013 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)