



Philips  
Ear hook Headphones



SHH4808



## Power bass for mobile phones

Secure grip with adjustable soft ear-hooks

Ultra-comfortable for active use, these adjustable earhook headphones with air-cushioned ear buds bring powerful sound enhanced by deep bass vents straight to your ears. Acoustics and cable length are optimised for use with mobile phones.

### Music to your ears

- Bass beat vents allow air movement for better sound

### Ultimate wearing comfort

- Secure grip with adjustable soft ear-hooks

### Always ready to go

- Anti-tangle slider
- Stays comfortably in your ear when you are on the move
- Extremely durable construction extends product life

### Fits your music phone

- Microphone-friendly cable length

**PHILIPS**  
sense and simplicity

# Specifications

## Sound

- Magnet type: Neodymium
- Diaphragm: Mylar dome
- Voice coil: Copper
- Frequency response: 12 - 23500 Hz Hz
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Speaker diameter: 13.5 mm
- Type: Dynamic
- Impedance: 16 Ohm

## Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 30 cm + 1 m
- Connector: 3.5 mm stereo
- Finishing of connector: Chrome-plated
- Type of cable: OFC

## Inner Carton

- EAN: 87 12581 49168 0
- Number of consumer packages: 6
- Gross weight: 0.426 kg
- Inner carton (L x W x H): 20.4 x 11.1 x 17.5 cm

- Net weight: 0.093 kg
- Tare weight: 0.333 kg

## Outer Box

- EAN: 87 12581 49167 3
- Number of consumer packages: 48
- Gross weight: 4.048 kg
- Outer carton (L x W x H): 44 x 24.8 x 39 cm
- Net weight: 0.744 kg
- Tare weight: 3.304 kg

## Packaging dimensions

- Packaging dimensions (W x H x D): 10.2 x 18 x 3.2 cm
- EAN: 87 12581 49166 6
- Number of products included: 1
- Packaging type: Blister
- Gross weight: 0.0555 kg
- Net weight: 0.0155 kg
- Tare weight: 0.04 kg

## Accessories

- Extension cable: 1 m

# Highlights

## Bass beat vents

Bass beat vents allow air movement for better sound with a deep rich bass

## Adjustable, soft ear-hooks

Easily adjust these soft ear-hooks for size by sliding the rubber inner part of the earhook up- or downwards. This can even be done while wearing the headphones for a secure, comfortable fit in any situation.

## Designed for active use

Whether you are out running, cycling or taking part in any active pastime, this headphone will stay comfortably in your ear.

## Extremely durable

You can be sure that the product will have an extra-long life thanks to its design, which allows it to withstand knocks and rough use, and the fact that it is made from strong materials.

## Anti-tangle slider

When storing your headphones there is a risk that the cables tangle if not stored carefully. This makes it a hassle to store the headphones and get them ready for listening. Simply slide the anti-tangle slider towards the earpieces to keep the two earpiece cables neatly together and to minimise the risk of the cables tangling.

## Mic-friendly headphones

The cable length of these headphones is designed to optimise sound pick up from the microphone of your headset connector. It also optimises the overall cable length of these headphones combined with a headset connector. Headset connectors allow the use of standard headphones (without a mic and with a standard 3.5 mm headphones plug) with a mobile phone. They often come with mobile phones but can also be purchased separately. For most mobile phone brands, Philips SHH1XXX headset connectors are available. It also optimises overall cable length to the mobile phone.



Issue date 2009-08-27

Version: 2.0.4

12 NC: 8670 000 54292  
EAN: 87 12581 49166 6

© 2009 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)