


Philips  
In-Ear Headphones



SHH7808



## Rich bass

from your mobile phone

If you are looking for balanced sound and dynamic bass from your mobile phone look no further. Front acoustic vents deliver dynamic bass and with its rugged construction these headphones are built to last.

### Enjoy quality sound

- Exceptional noise isolation for quality sound at low volume
- Acoustics vent control low frequencies for deep clean bass

### Ultimate wearing comfort

- 3 sizes of ultra-soft silicone caps ensure an ideal fit

### Fits your music phone

- Microphone-friendly cable length

### Always ready to go

- Split cable enables convenient remote control connection
- Durable Flexi-Grip makes a strong flexible connection
- Anti-tangle slider

# PHILIPS

# Specifications

## Sound

- Magnet type: Neodymium
- Frequency response: 8 - 23 500 Hz
- Sensitivity: 98 dB
- Maximum power input: 50 mW
- Impedance: 16 ohm at 1 kHz
- Speaker diameter: 8.6 mm
- Type: Dynamic

## Connectivity

- Cable length: 30 cm + 1 m
- Connector: 3.5 mm stereo

## Accessories

- Extension cable: 1 m

## Packaging dimensions

- EAN: 87 12581 45019 9
- Number of products included: 1
- Packaging dimensions (W x H x D): 10.2 x 18 x 3.2 cm

- Net weight: 0.011 kg
- Gross weight: 0.0525 kg
- Tare weight: 0.0415 kg
- Packaging type: Blister

## Outer Carton

- EAN: 87 12581 45020 5
- Number of consumer packages: 96
- Outer carton (L x W x H): 46.6 x 43 x 39 cm
- Net weight: 1.056 kg
- Gross weight: 7.7885 kg
- Tare weight: 6.7325 kg

## Inner Carton

- EAN: 87 12581 45021 2
- Number of consumer packages: 6
- Inner carton (L x W x H): 20.4 x 11.1 x 17.5 cm
- Net weight: 0.066 kg
- Gross weight: 0.416 kg
- Tare weight: 0.35 kg

# Highlights

## Mic-friendly headphones

The cable length of these headphones is designed to optimise sound pick up from the microphone of your headset connector. It also optimises the overall cable length of these headphones combined with a headset connector. Headset connectors allow the use of standard headphones (without a mic and with a standard 3.5 mm headphones plug) with a mobile phone. They often come with mobile phones but can also be purchased separately. For most mobile phone brands, Philips SHH1XXXX headset connectors are available. It also optimises overall cable length to the mobile phone.

## Flexi-grip design

The soft flexi-grip material that the body of the headphone is sheathed in enhances its performance and extends its durability. It protects the cable connection from damage that otherwise could occur due to repeated bending of the headphone body from frequent contact with the user's fingertips when being put on and removed.

## Split cable

This standard cable has a 3.5 mm socket on one end and a 3.5 mm plug on the other for extending your freedom of movement with headphones.

## 3-size ultra-soft silicone cap

Available in three different sizes (small, medium and large), the interchangeable ear caps ensure a personalised fit for each individual user. They are also made from ultra-soft silicone to provide the utmost comfort for prolonged listening.



Issue date 2013-09-19

Version: 2.0.3

12 NC: 8670 000 47334  
EAN: 87 12581 45019 9

© 2013 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)